

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787575

Luminaire Tested: LER6D05D010-EC6DR150210IC9035-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR150210IC9035-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 658.4 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P787575
CATALOG NUMBER: LER6D05D010-EC6DR150210IC9035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P787575

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1009394	1009394	1009394
5°	593167	585484	590118
10°	177032	178273	180998
15°	44036	44896	43507
20°	13173	15260	13452
25°	4643	5920	4705
30°	1707	2246	1737
35°	857	966	828
40°	540	597	540
45°	399	427	399
50°	320	320	320
55°	264	264	264
60°	211	211	211
65°	164	164	164
70°	139	139	139
75°	83	83	113
80°	63	63	63
85°	33	33	33

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 427 cd/sqm



TEST NUMBER: P787575

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.0	64.9
10°-20°	175.6	26.7
20°-30°	34.9	5.3
30°-40°	8.7	1.3
40°-50°	4.6	0.7
50°-60°	3.4	0.5
60°-70°	2.4	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	637.6	96.8
0°-40°	646.3	98.2
0°-60°	654.3	99.4
0°-90°	658.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	658.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8971	8971	8971	8971	8971	
5°	5837	5777	5761	5801	5807	426
15°	507	516	517	508	501	174
25°	60	68	76	67	60	31
35°	12	12	13	12	11	8
45°	6	6	6	6	6	4
55°	4	4	4	4	4	3
65°	2	2	2	2	2	2
75°	1	1	1	1	2	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P787575

CATALOG NUMBER: LER6D05D010-EC6DR150210IC9035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8970.8	8970.8	8970.8	8970.8	8970.8
2.5°	8092.0	8098.8	8101.5	8109.5	8139.1
5°	5836.6	5776.6	5761.0	5800.9	5806.6
7.5°	3457.4	3469.5	3514.0	3523.8	3488.1
10°	1897.3	1912.9	1910.6	1924.3	1939.8
12.5°	970.3	958.1	954.3	969.9	948.3
15°	507.0	516.5	516.9	507.7	500.9
17.5°	272.7	283.7	301.9	287.1	264.3
20°	161.0	170.9	186.5	174.3	164.4
22.5°	99.5	107.5	118.5	109.0	101.0
25°	59.6	67.6	76.0	67.2	60.4
27.5°	35.3	42.2	47.5	41.8	34.9
30°	22.8	26.6	30.0	26.2	23.2
32.5°	16.0	17.5	19.0	17.5	16.0
35°	11.8	12.5	13.3	12.5	11.4
37.5°	9.1	9.9	10.3	9.5	8.7
40°	7.6	8.0	8.4	8.0	7.6
42.5°	6.5	6.8	6.8	6.8	6.5
45°	5.7	5.7	6.1	5.7	5.7
47.5°	4.9	4.9	5.3	4.9	4.9
50°	4.6	4.6	4.6	4.6	4.6
52.5°	4.2	4.2	4.2	4.2	4.2
55°	3.8	3.8	3.8	3.8	3.8
57.5°	3.4	3.4	3.4	3.4	3.4
60°	3.0	3.0	3.0	3.0	3.0
62.5°	2.7	2.7	2.7	2.7	2.7
65°	2.3	2.3	2.3	2.3	2.3
67.5°	2.3	2.3	2.3	2.3	2.3
70°	1.9	1.9	1.9	1.9	1.9
72.5°	1.5	1.5	1.5	1.5	1.5
75°	1.1	1.1	1.1	1.1	1.5
77.5°	1.1	1.1	1.1	1.1	1.1
80°	0.8	0.8	0.8	0.8	0.8
82.5°	0.8	0.8	0.8	0.8	0.8
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)