

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789165

Luminaire Tested: LER6D10D010-EC6DR500210IC9035-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789165  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR500210IC9035-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2195.7 lumens  
Efficiency: N/A  
Efficacy: 187.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789165  
CATALOG NUMBER: LER6D10D010-EC6DR500210IC9035-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P789165

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9035-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |     |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|-----|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |     |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |    |    |     |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 0   |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |     |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    | 100 |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 102 | 102 | 101 | 99  | 98  | 97  | 97  | 95  |    |    |    |    |    | 95  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 95  | 97  | 95  | 93  | 95  | 93  | 91  | 90  |    |    |    |    |    | 90  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 85  |    |    |    |    |    | 85  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 90  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 80  |    |    |    |    |    | 80  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 79  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  |    |    |    |    |    | 76  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 74  | 72  |    |    |    |    |    | 72  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |    |    |    |    |    | 69  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 85  | 76  | 71  | 67  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 66  | 65  |    |    |    |    |    | 65  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 67  | 64  | 71  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  |    |    |    |    |    | 62  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 78  | 70  | 64  | 61  | 77  | 69  | 64  | 61  | 68  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 60  | 59  |    |    |    |    |    | 59  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 386543 |
| 5°  | 382480 |
| 10° | 376186 |
| 15° | 342546 |
| 20° | 285043 |
| 25° | 202341 |
| 30° | 107100 |
| 35° | 43643  |
| 40° | 16203  |
| 45° | 7417   |
| 50° | 3043   |
| 55° | 1600   |
| 60° | 787    |
| 65° | 233    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7417 cd/sqm



TEST NUMBER: P789165

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9035-6LBS1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 329.6  | 15.0      |
| 10°-20°   | 833.0  | 37.9      |
| 20°-30°   | 748.3  | 34.1      |
| 30°-40°   | 234.3  | 10.7      |
| 40°-50°   | 41.0   | 1.9       |
| 50°-60°   | 8.2    | 0.4       |
| 60°-70°   | 1.2    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1910.9 | 87.0      |
| 0°-40°    | 2145.2 | 97.7      |
| 0°-60°    | 2194.4 | 99.9      |
| 0°-90°    | 2195.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2195.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3538 |      |
| 5°  | 3487 | 330  |
| 15° | 3028 | 833  |
| 25° | 1678 | 748  |
| 35° | 327  | 234  |
| 45° | 48   | 41   |
| 55° | 8    | 8    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P789165  
CATALOG NUMBER: LER6D10D010-EC6DR500210IC9035-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3537.8 |
| 2.5°  | 3520.2 |
| 5°    | 3487.3 |
| 7.5°  | 3437.2 |
| 10°   | 3390.7 |
| 12.5° | 3241.6 |
| 15°   | 3028.3 |
| 17.5° | 2757.5 |
| 20°   | 2451.5 |
| 22.5° | 2097.4 |
| 25°   | 1678.4 |
| 27.5° | 1233.9 |
| 30°   | 848.9  |
| 32.5° | 552.7  |
| 35°   | 327.2  |
| 37.5° | 187.9  |
| 40°   | 113.6  |
| 42.5° | 74.0   |
| 45°   | 48.0   |
| 47.5° | 29.2   |
| 50°   | 17.9   |
| 52.5° | 12.2   |
| 55°   | 8.4    |
| 57.5° | 5.7    |
| 60°   | 3.6    |
| 62.5° | 2.1    |
| 65°   | 0.9    |
| 67.5° | 0.3    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)