

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789282

Luminaire Tested: LER6D10D010-EC6DR650210IC9024-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789282  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR650210IC9024-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1196.5 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P789282

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P789282

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80				
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75				
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69				
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65				
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60				
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57				
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53				
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	128709
5°	128817
10°	133357
15°	133578
20°	122982
25°	104787
30°	80215
35°	56674
40°	33447
45°	13582
50°	4929
55°	2743
60°	1573
65°	853
70°	894
75°	718
80°	755
85°	627

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13582 cd/sqm



TEST NUMBER: P789282

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.4	9.5
10°-20°	327.2	27.3
20°-30°	392.6	32.8
30°-40°	263.8	22.1
40°-50°	79.0	6.6
50°-60°	14.0	1.2
60°-70°	3.9	0.3
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.2	69.6
0°-40°	1097.1	91.7
0°-60°	1190.0	99.5
0°-90°	1196.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1196.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1178	
5°	1174	113
15°	1181	327
25°	869	393
35°	425	264
45°	88	79
55°	14	14
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P789282

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1178.0
2.5°	1183.0
5°	1174.5
7.5°	1192.2
10°	1202.0
12.5°	1199.6
15°	1180.9
17.5°	1135.0
20°	1057.7
22.5°	966.6
25°	869.2
27.5°	759.2
30°	635.8
32.5°	524.0
35°	424.9
37.5°	326.9
40°	234.5
42.5°	153.2
45°	87.9
47.5°	46.5
50°	29.0
52.5°	20.1
55°	14.4
57.5°	10.4
60°	7.2
62.5°	4.7
65°	3.3
67.5°	3.0
70°	2.8
72.5°	2.2
75°	1.7
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)