

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789313

Luminaire Tested: LER6D10D010-EC6DR650210IC9040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR650210IC9040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1810.7 lumens
Efficiency: N/A
Efficacy: 154.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789313

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789313

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | | | | | | | | | | | | | | | | | |
| 4 | 97 | 89 | 84 | 79 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | | | | | | | | | | | | | | | | | |
| 5 | 92 | 83 | 78 | 73 | 90 | 83 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 72 | 77 | 74 | 71 | 69 | | | | | | | | | | | | | | | | | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | | | | | | | | | | | | | | | | | | | |
| 7 | 83 | 73 | 67 | 63 | 81 | 73 | 67 | 63 | 71 | 66 | 62 | 70 | 66 | 62 | 69 | 65 | 62 | 60 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 62 | 58 | 65 | 61 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 65 | 59 | 55 | 74 | 65 | 59 | 55 | 64 | 58 | 55 | 63 | 58 | 55 | 62 | 58 | 54 | 53 | | | | | | | | | | | | | | | | | | | |
| 10 | 71 | 61 | 56 | 52 | 70 | 61 | 55 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 59 | 54 | 51 | 50 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|--------|
| 0° | 194779 |
| 5° | 194942 |
| 10° | 201800 |
| 15° | 202137 |
| 20° | 186095 |
| 25° | 158567 |
| 30° | 121394 |
| 35° | 85765 |
| 40° | 50619 |
| 45° | 20551 |
| 50° | 7445 |
| 55° | 4153 |
| 60° | 2382 |
| 65° | 1319 |
| 70° | 1374 |
| 75° | 1055 |
| 80° | 1133 |
| 85° | 1003 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20551 cd/sqm



TEST NUMBER: P789313

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 171.7 | 9.5 |
| 10°-20° | 495.2 | 27.3 |
| 20°-30° | 594.1 | 32.8 |
| 30°-40° | 399.3 | 22.1 |
| 40°-50° | 119.5 | 6.6 |
| 50°-60° | 21.1 | 1.2 |
| 60°-70° | 6.0 | 0.3 |
| 70°-80° | 2.9 | 0.2 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1260.9 | 69.6 |
| 0°-40° | 1660.2 | 91.7 |
| 0°-60° | 1800.8 | 99.5 |
| 0°-90° | 1810.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1810.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1783 | |
| 5° | 1777 | 172 |
| 15° | 1787 | 495 |
| 25° | 1315 | 594 |
| 35° | 643 | 399 |
| 45° | 133 | 120 |
| 55° | 22 | 21 |
| 65° | 5 | 6 |
| 75° | 2 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P789313

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1782.7 |
| 2.5° | 1790.3 |
| 5° | 1777.4 |
| 7.5° | 1804.2 |
| 10° | 1818.9 |
| 12.5° | 1815.4 |
| 15° | 1787.0 |
| 17.5° | 1717.6 |
| 20° | 1600.5 |
| 22.5° | 1462.7 |
| 25° | 1315.3 |
| 27.5° | 1148.9 |
| 30° | 962.2 |
| 32.5° | 792.9 |
| 35° | 643.0 |
| 37.5° | 494.8 |
| 40° | 354.9 |
| 42.5° | 231.8 |
| 45° | 133.0 |
| 47.5° | 70.4 |
| 50° | 43.8 |
| 52.5° | 30.4 |
| 55° | 21.8 |
| 57.5° | 15.7 |
| 60° | 10.9 |
| 62.5° | 7.1 |
| 65° | 5.1 |
| 67.5° | 4.6 |
| 70° | 4.3 |
| 72.5° | 3.3 |
| 75° | 2.5 |
| 77.5° | 2.3 |
| 80° | 1.8 |
| 82.5° | 1.3 |
| 85° | 0.8 |
| 87.5° | 0.5 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)