

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789328

Luminaire Tested: LER6D10D010-EC6DR700210IC9024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR700210IC9024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1597.4 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789328
CATALOG NUMBER: LER6D10D010-EC6DR700210IC9024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789328

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196232
5°	190401
10°	185103
15°	182670
20°	170572
25°	128151
30°	90585
35°	32092
40°	16873
45°	17970
50°	18613
55°	18954
60°	19077
65°	18666
70°	17634
75°	16337
80°	14472
85°	11784

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 19077 cd/sqm



TEST NUMBER: P789328

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.7	10.3
10°-20°	449.2	28.1
20°-30°	494.7	31.0
30°-40°	189.0	11.8
40°-50°	89.2	5.6
50°-60°	88.7	5.6
60°-70°	71.0	4.4
70°-80°	40.8	2.6
80°-90°	11.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1107.6	69.3
0°-40°	1296.6	81.2
0°-60°	1474.5	92.3
0°-90°	1597.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1597.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1796	
5°	1736	164
15°	1615	449
25°	1063	495
35°	241	189
45°	116	89
55°	100	89
65°	72	71
75°	39	41
85°	9	11
90°	0	



TEST NUMBER: P789328

CATALOG NUMBER: LER6D10D010-EC6DR700210IC9024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1796.0
2.5°	1777.3
5°	1736.0
7.5°	1701.6
10°	1668.4
12.5°	1640.2
15°	1614.9
17.5°	1553.8
20°	1467.0
22.5°	1279.9
25°	1063.0
27.5°	925.3
30°	718.0
32.5°	463.8
35°	240.6
37.5°	130.0
40°	118.3
42.5°	117.4
45°	116.3
47.5°	113.7
50°	109.5
52.5°	104.6
55°	99.5
57.5°	93.8
60°	87.3
62.5°	79.9
65°	72.2
67.5°	63.7
70°	55.2
72.5°	46.6
75°	38.7
77.5°	30.4
80°	23.0
82.5°	16.2
85°	9.4
87.5°	3.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)