

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787954

Luminaire Tested: LER6D05D010-EC6DR550210IC9030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P787954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR550210IC9030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1079.7 lumens
Efficiency: N/A
Efficacy: 144.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P787954

CATALOG NUMBER: LER6D05D010-EC6DR550210IC9030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P787954

CATALOG NUMBER: LER6D05D010-EC6DR550210IC9030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94	94													
	2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87													
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81													
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75													
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70													
	6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65	65	65	65	65													
	7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61	61	61	61	61	61													
	8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57	57	57	57	57	57													
	9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54	54	54	54	54	54													
	10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132282
5°	127029
10°	126545
15°	122911
20°	110203
25°	91080
30°	68797
35°	49885
40°	31921
45°	14587
50°	4776
55°	2057
60°	896
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14587 cd/sqm



TEST NUMBER: P787954

CATALOG NUMBER: LER6D05D010-EC6DR550210IC9030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.2	10.2
10°-20°	300.8	27.9
20°-30°	342.7	31.7
30°-40°	233.3	21.6
40°-50°	80.4	7.4
50°-60°	11.1	1.0
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.7	69.8
0°-40°	987.1	91.4
0°-60°	1078.6	99.9
0°-90°	1079.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1079.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1211	
5°	1158	110
15°	1087	301
25°	756	343
35°	374	233
45°	94	80
55°	11	11
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P787954

CATALOG NUMBER: LER6D05D010-EC6DR550210IC9030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1210.7
2.5°	1182.9
5°	1158.2
7.5°	1146.0
10°	1140.6
12.5°	1122.6
15°	1086.6
17.5°	1029.5
20°	947.8
22.5°	853.6
25°	755.5
27.5°	653.3
30°	545.3
32.5°	453.8
35°	374.0
37.5°	298.1
40°	223.8
42.5°	155.1
45°	94.4
47.5°	50.9
50°	28.1
52.5°	16.7
55°	10.8
57.5°	6.9
60°	4.1
62.5°	1.8
65°	0.5
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)