

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787985

Luminaire Tested: LER6D05D010-EC6DR600210IC9024-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787985  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR600210IC9024-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1059.5 lumens  
Efficiency: N/A  
Efficacy: 141.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P787985

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9024-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P787985

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9024-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	137483
5°	140871
10°	142566
15°	135817
20°	119749
25°	96855
30°	65517
35°	32825
40°	5320
45°	5207
50°	5320
55°	5391
60°	5550
65°	5662
70°	5814
75°	5868
80°	5663
85°	4764

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 5868 cd/sqm



TEST NUMBER: P787985

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9024-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.8	11.6
10°-20°	332.1	31.3
20°-30°	357.3	33.7
30°-40°	155.3	14.7
40°-50°	26.1	2.5
50°-60°	25.4	2.4
60°-70°	21.7	2.0
70°-80°	14.5	1.4
80°-90°	4.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.2	76.7
0°-40°	967.5	91.3
0°-60°	1019.0	96.2
0°-90°	1059.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1059.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1258	
5°	1284	123
15°	1201	332
25°	803	357
35°	246	155
45°	34	26
55°	28	25
65°	22	22
75°	14	15
85°	4	4
90°	0	



TEST NUMBER: P787985

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9024-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1258.3
2.5°	1293.7
5°	1284.4
7.5°	1287.3
10°	1285.0
12.5°	1258.5
15°	1200.7
17.5°	1123.1
20°	1029.9
22.5°	930.2
25°	803.4
27.5°	642.6
30°	519.3
32.5°	400.2
35°	246.1
37.5°	105.3
40°	37.3
42.5°	34.4
45°	33.7
47.5°	32.6
50°	31.3
52.5°	29.8
55°	28.3
57.5°	26.9
60°	25.4
62.5°	23.7
65°	21.9
67.5°	20.1
70°	18.2
72.5°	16.0
75°	13.9
77.5°	11.5
80°	9.0
82.5°	6.4
85°	3.8
87.5°	1.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)