

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788017

Luminaire Tested: LER6D05D010-EC6DR600210IC9040-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788017  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR600210IC9040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1317.5 lumens  
Efficiency: N/A  
Efficacy: 175.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788017  
CATALOG NUMBER: LER6D05D010-EC6DR600210IC9040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P788017

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	170960
5°	175167
10°	177281
15°	168892
20°	148911
25°	120435
30°	81464
35°	40828
40°	6618
45°	6474
50°	6612
55°	6705
60°	6905
65°	7058
70°	7220
75°	7303
80°	7047
85°	5892

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 7303 cd/sqm



TEST NUMBER: P788017

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9040-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.6	11.6
10°-20°	413.0	31.3
20°-30°	444.3	33.7
30°-40°	193.1	14.7
40°-50°	32.4	2.5
50°-60°	31.6	2.4
60°-70°	27.0	2.0
70°-80°	18.1	1.4
80°-90°	5.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1010.0	76.7
0°-40°	1203.1	91.3
0°-60°	1267.1	96.2
0°-90°	1317.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1317.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1565	
5°	1597	153
15°	1493	413
25°	999	444
35°	306	193
45°	42	32
55°	35	32
65°	27	27
75°	17	18
85°	5	5
90°	0	



TEST NUMBER: P788017

CATALOG NUMBER: LER6D05D010-EC6DR600210IC9040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1564.7
2.5°	1608.7
5°	1597.1
7.5°	1600.8
10°	1597.9
12.5°	1564.9
15°	1493.1
17.5°	1396.5
20°	1280.7
22.5°	1156.6
25°	999.0
27.5°	799.1
30°	645.7
32.5°	497.7
35°	306.1
37.5°	130.9
40°	46.4
42.5°	42.8
45°	41.9
47.5°	40.5
50°	38.9
52.5°	37.1
55°	35.2
57.5°	33.4
60°	31.6
62.5°	29.5
65°	27.3
67.5°	25.0
70°	22.6
72.5°	20.0
75°	17.3
77.5°	14.3
80°	11.2
82.5°	7.9
85°	4.7
87.5°	1.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)