

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788037

Luminaire Tested: LER6D05D010-EC6DR650210IC9024-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788037  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR650210IC9024-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 974.6 lumens  
Efficiency: N/A  
Efficacy: 129.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788037  
CATALOG NUMBER: LER6D05D010-EC6DR650210IC9024-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P788037

CATALOG NUMBER: LER6D05D010-EC6DR650210IC9024-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	51676
5°	51545
10°	51506
15°	49913
20°	45439
25°	39599
30°	32937
35°	26095
40°	18839
45°	11902
50°	6206
55°	3299
60°	1729
65°	954
70°	393
75°	451
80°	303
85°	268

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11902 cd/sqm



TEST NUMBER: P788037

CATALOG NUMBER: LER6D05D010-EC6DR650210IC9024-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.7	8.6
10°-20°	229.1	23.5
20°-30°	280.1	28.7
30°-40°	227.2	23.3
40°-50°	113.3	11.6
50°-60°	31.6	3.2
60°-70°	7.2	0.7
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.9	60.8
0°-40°	820.1	84.2
0°-60°	965.0	99.0
0°-90°	974.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	885	
5°	879	84
15°	826	229
25°	614	280
35°	366	227
45°	144	113
55°	32	32
65°	7	7
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P788037

CATALOG NUMBER: LER6D05D010-EC6DR650210IC9024-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	884.8
2.5°	884.2
5°	879.2
7.5°	876.4
10°	868.5
12.5°	852.3
15°	825.5
17.5°	783.7
20°	731.1
22.5°	674.5
25°	614.5
27.5°	550.4
30°	488.4
32.5°	427.1
35°	366.0
37.5°	305.0
40°	247.1
42.5°	192.7
45°	144.1
47.5°	100.4
50°	68.3
52.5°	47.1
55°	32.4
57.5°	21.8
60°	14.8
62.5°	10.3
65°	6.9
67.5°	3.5
70°	2.3
72.5°	2.2
75°	2.0
77.5°	1.3
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)