

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789462

Luminaire Tested: LER6D15D010-EC6DR1515309050-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR1515309050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1512.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789462
CATALOG NUMBER: LER6D15D010-EC6DR1515309050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789462

CATALOG NUMBER: LER6D15D010-EC6DR1515309050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2318181	2318181	2318181
5°	1362274	1344632	1355272
10°	406578	409424	415695
15°	101127	103099	99920
20°	30258	35037	30904
25°	10665	13586	10805
30°	3916	5159	3984
35°	1961	2215	1903
40°	1236	1363	1236
45°	917	980	917
50°	730	730	730
55°	606	606	606
60°	491	491	491
65°	371	371	371
70°	322	322	322
75°	197	197	265
80°	134	134	134
85°	75	75	75

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 980 cd/sqm



TEST NUMBER: P789462

CATALOG NUMBER: LER6D15D010-EC6DR1515309050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	980.7	64.9
10°-20°	403.4	26.7
20°-30°	80.1	5.3
30°-40°	20.0	1.3
40°-50°	10.5	0.7
50°-60°	7.8	0.5
60°-70°	5.5	0.4
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1464.2	96.8
0°-40°	1484.2	98.2
0°-60°	1502.5	99.4
0°-90°	1512.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1512.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20602	20602	20602	20602	20602	
5°	13404	13267	13231	13322	13336	979
15°	1164	1186	1187	1166	1150	399
25°	137	155	174	154	139	72
35°	27	29	30	29	26	18
45°	13	13	14	13	13	10
55°	9	9	9	9	9	8
65°	5	5	5	5	5	5
75°	3	3	3	3	4	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P789462

CATALOG NUMBER: LER6D15D010-EC6DR1515309050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20602.4	20602.4	20602.4	20602.4	20602.4
2.5°	18584.2	18599.9	18606.0	18624.4	18692.4
5°	13404.4	13266.6	13230.8	13322.4	13335.5
7.5°	7940.3	7968.2	8070.2	8092.9	8010.9
10°	4357.4	4393.1	4387.9	4419.3	4455.1
12.5°	2228.4	2200.5	2191.8	2227.5	2177.8
15°	1164.3	1186.2	1187.0	1166.1	1150.4
17.5°	626.2	651.5	693.4	659.4	607.0
20°	369.8	392.5	428.2	400.3	377.7
22.5°	228.5	246.8	272.1	250.3	232.0
25°	136.9	155.2	174.4	154.4	138.7
27.5°	81.1	96.8	109.0	95.9	80.2
30°	52.3	61.1	68.9	60.2	53.2
32.5°	36.6	40.1	43.6	40.1	36.6
35°	27.0	28.8	30.5	28.8	26.2
37.5°	20.9	22.7	23.5	21.8	20.1
40°	17.4	18.3	19.2	18.3	17.4
42.5°	14.8	15.7	15.7	15.7	14.8
45°	13.1	13.1	14.0	13.1	13.1
47.5°	11.3	11.3	12.2	11.3	11.3
50°	10.5	10.5	10.5	10.5	10.5
52.5°	9.6	9.6	9.6	9.6	9.6
55°	8.7	8.7	8.7	8.7	8.7
57.5°	7.8	7.8	7.8	7.8	7.8
60°	7.0	7.0	7.0	7.0	7.0
62.5°	6.1	6.1	6.1	6.1	6.1
65°	5.2	5.2	5.2	5.2	5.2
67.5°	5.2	5.2	5.2	5.2	5.2
70°	4.4	4.4	4.4	4.4	4.4
72.5°	3.5	3.5	3.5	3.5	3.5
75°	2.6	2.6	2.6	2.6	3.5
77.5°	2.6	2.6	2.6	2.6	2.6
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.9	0.9	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)