

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789471

Luminaire Tested: LER6D15D010-EC6DR2015309024-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789471  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR2015309024-6LBDDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1355.7 lumens  
Efficiency: N/A  
Efficacy: 85.8 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789471  
CATALOG NUMBER: LER6D15D010-EC6DR2015309024-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P789471

CATALOG NUMBER: LER6D15D010-EC6DR2015309024-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	93															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	91															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	92	90	89															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	90	88	87															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	88	86	85															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	86	84	83															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	84	82	81															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	843078
5°	760618
10°	426899
15°	217000
20°	91879
25°	42412
30°	22457
35°	12098
40°	6461
45°	3817
50°	2227
55°	1181
60°	743
65°	543
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3817 cd/sqm



TEST NUMBER: P789471

CATALOG NUMBER: LER6D15D010-EC6DR2015309024-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	549.4	40.5
10°-20°	541.0	39.9
20°-30°	176.7	13.0
30°-40°	60.2	4.4
40°-50°	20.2	1.5
50°-60°	6.1	0.4
60°-70°	2.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1267.1	93.5
0°-40°	1327.3	97.9
0°-60°	1353.6	99.8
0°-90°	1355.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7716	
5°	6935	549
15°	1918	541
25°	352	177
35°	91	60
45°	25	20
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789471

CATALOG NUMBER: LER6D15D010-EC6DR2015309024-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7716.2
0.5°	7716.2
1°	7706.6
1.5°	7687.4
2°	7652.3
2.5°	7605.6
3°	7539.6
3.5°	7447.6
4°	7310.8
4.5°	7144.6
5°	6935.0
5.5°	6659.5
6°	6377.1
6.5°	6053.4
7°	5736.7
7.5°	5365.6
8°	5034.4
8.5°	4701.2
9°	4393.4
9.5°	4111.0
10°	3847.8
12.5°	2762.9
15°	1918.4
17.5°	1253.3
20°	790.2
22.5°	511.9
25°	351.8
27.5°	247.4
30°	178.0
32.5°	127.8
35°	90.7
37.5°	63.2
40°	45.3
42.5°	33.0
45°	24.7
47.5°	19.2
50°	13.1
52.5°	8.2
55°	6.2
57.5°	4.8
60°	3.4
62.5°	2.7
65°	2.1



TEST NUMBER: P789471  
CATALOG NUMBER: LER6D15D010-EC6DR2015309024-6LBDP1LI

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.4
70°		0.7

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)