

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789489

Luminaire Tested: LER6D15D010-EC6DR2015309030-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789489  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR2015309030-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1457.8 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789489  
CATALOG NUMBER: LER6D15D010-EC6DR2015309030-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P789489

CATALOG NUMBER: LER6D15D010-EC6DR2015309030-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81	78	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	906558
5°	817881
10°	459040
15°	233334
20°	98797
25°	45606
30°	24148
35°	13005
40°	6960
45°	4110
50°	2380
55°	1257
60°	809
65°	569
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4110 cd/sqm



TEST NUMBER: P789489

CATALOG NUMBER: LER6D15D010-EC6DR2015309030-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	590.7	40.5
10°-20°	581.7	39.9
20°-30°	190.0	13.0
30°-40°	64.7	4.4
40°-50°	21.8	1.5
50°-60°	6.5	0.4
60°-70°	2.2	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1362.5	93.5
0°-40°	1427.2	97.9
0°-60°	1455.5	99.8
0°-90°	1457.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1457.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8297	
5°	7457	591
15°	2063	582
25°	378	190
35°	98	65
45°	27	22
55°	7	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789489

CATALOG NUMBER: LER6D15D010-EC6DR2015309030-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8297.2
0.5°	8297.2
1°	8286.8
1.5°	8266.1
2°	8228.5
2.5°	8178.2
3°	8107.3
3.5°	8008.3
4°	7861.3
4.5°	7682.5
5°	7457.1
5.5°	7160.8
6°	6857.2
6.5°	6509.2
7°	6168.6
7.5°	5769.6
8°	5413.5
8.5°	5055.1
9°	4724.1
9.5°	4420.5
10°	4137.5
12.5°	2970.9
15°	2062.8
17.5°	1347.6
20°	849.7
22.5°	550.4
25°	378.3
27.5°	266.0
30°	191.4
32.5°	137.4
35°	97.5
37.5°	68.0
40°	48.8
42.5°	35.5
45°	26.6
47.5°	20.7
50°	14.0
52.5°	8.9
55°	6.6
57.5°	5.2
60°	3.7
62.5°	3.0
65°	2.2



TEST NUMBER: P789489  
CATALOG NUMBER: LER6D15D010-EC6DR2015309030-6LBS1B

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.5
70°		0.7

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)