

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788105

Luminaire Tested: LER6D05D010-EC6DR700210IC9035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D05D010-EC6DR700210IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1290.5 lumens
Efficiency: N/A
Efficacy: 172.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788105

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P788105

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158526
5°	153813
10°	149522
15°	147559
20°	137795
25°	103521
30°	73175
35°	25916
40°	13635
45°	14525
50°	15026
55°	15315
60°	15406
65°	15072
70°	14248
75°	13171
80°	11703
85°	9528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 15414 cd/sqm



TEST NUMBER: P788105

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	10.3
10°-20°	362.8	28.1
20°-30°	399.6	31.0
30°-40°	152.7	11.8
40°-50°	72.1	5.6
50°-60°	71.7	5.6
60°-70°	57.4	4.4
70°-80°	33.0	2.6
80°-90°	9.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.7	69.3
0°-40°	1047.4	81.2
0°-60°	1191.2	92.3
0°-90°	1290.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1290.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1451	
5°	1402	132
15°	1304	363
25°	859	400
35°	194	153
45°	94	72
55°	80	72
65°	58	57
75°	31	33
85°	8	9
90°	0	



TEST NUMBER: P788105

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1450.9
2.5°	1435.7
5°	1402.4
7.5°	1374.6
10°	1347.7
12.5°	1325.0
15°	1304.5
17.5°	1255.2
20°	1185.1
22.5°	1033.9
25°	858.7
27.5°	747.5
30°	580.0
32.5°	374.7
35°	194.3
37.5°	105.0
40°	95.6
42.5°	94.9
45°	94.0
47.5°	91.9
50°	88.4
52.5°	84.5
55°	80.4
57.5°	75.8
60°	70.5
62.5°	64.5
65°	58.3
67.5°	51.5
70°	44.6
72.5°	37.7
75°	31.2
77.5°	24.6
80°	18.6
82.5°	13.1
85°	7.6
87.5°	3.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)