

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788112

Luminaire Tested: LER6D05D010-EC6DR700210IC9040-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788112  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D05D010-EC6DR700210IC9040-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1263.0 lumens  
Efficiency: N/A  
Efficacy: 168.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P788112  
CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P788112

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	155150
5°	150544
10°	146338
15°	144425
20°	134865
25°	101315
30°	71623
35°	25369
40°	13336
45°	14216
50°	14720
55°	14992
60°	15078
65°	14762
70°	13928
75°	12918
80°	11452
85°	9277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 15089 cd/sqm



TEST NUMBER: P788112

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.5	10.3
10°-20°	355.1	28.1
20°-30°	391.1	31.0
30°-40°	149.4	11.8
40°-50°	70.6	5.6
50°-60°	70.1	5.6
60°-70°	56.2	4.4
70°-80°	32.3	2.6
80°-90°	8.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	875.7	69.3
0°-40°	1025.1	81.2
0°-60°	1165.8	92.3
0°-90°	1263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1263.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1420	
5°	1373	129
15°	1277	355
25°	840	391
35°	190	149
45°	92	71
55°	79	70
65°	57	56
75°	31	32
85°	7	9
90°	0	



TEST NUMBER: P788112

CATALOG NUMBER: LER6D05D010-EC6DR700210IC9040-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1420.0
2.5°	1405.2
5°	1372.6
7.5°	1345.4
10°	1319.0
12.5°	1296.8
15°	1276.8
17.5°	1228.4
20°	1159.9
22.5°	1011.9
25°	840.4
27.5°	731.6
30°	567.7
32.5°	366.7
35°	190.2
37.5°	102.7
40°	93.5
42.5°	92.9
45°	92.0
47.5°	89.9
50°	86.6
52.5°	82.7
55°	78.7
57.5°	74.2
60°	69.0
62.5°	63.2
65°	57.1
67.5°	50.4
70°	43.6
72.5°	36.9
75°	30.6
77.5°	24.1
80°	18.2
82.5°	12.8
85°	7.4
87.5°	2.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)