

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789587

Luminaire Tested: LER6D15D010-EC6DR300215IC9035-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9035-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2023.1 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789587

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P789587

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	497922	497922	497922
5°	483627	483067	483658
10°	418895	415941	418801
15°	273311	271845	270474
20°	135901	141000	135722
25°	68460	77201	67058
30°	27408	29865	23882
35°	12717	12176	10204
40°	5486	6095	5166
45°	3875	4806	3908
50°	1334	3501	1405
55°	761	1455	814
60°	536	643	536
65°	344	344	344
70°	224	134	224
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 4806 cd/sqm



TEST NUMBER: P789587

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	572.0	28.3
10°-20°	921.3	45.5
20°-30°	398.1	19.7
30°-40°	90.7	4.5
40°-50°	31.1	1.5
50°-60°	7.6	0.4
60°-70°	2.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1891.4	93.5
0°-40°	1982.1	98.0
0°-60°	2020.9	99.9
0°-90°	2023.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2023.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6505	6505	6505	6505	6505	
5°	6294	6288	6287	6300	6295	572
15°	3449	3408	3430	3419	3413	924
25°	811	841	914	820	794	388
35°	136	139	130	129	109	92
45°	36	44	44	44	36	25
55°	6	6	11	6	6	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P789587

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6505.1	6505.1	6505.1	6505.1	6505.1
2.5°	6462.0	6457.6	6460.1	6463.3	6464.6
5°	6294.3	6288.3	6287.0	6300.1	6294.7
7.5°	5956.1	5947.5	5934.4	5964.1	5991.9
10°	5389.5	5380.0	5351.5	5365.6	5388.3
12.5°	4553.1	4522.1	4521.5	4566.2	4560.1
15°	3449.0	3407.5	3430.5	3419.3	3413.2
17.5°	2319.3	2303.4	2334.0	2324.8	2284.8
20°	1668.4	1672.6	1731.0	1701.7	1666.2
22.5°	1217.5	1232.5	1301.8	1226.1	1198.3
25°	810.6	841.2	914.1	819.8	794.0
27.5°	498.6	512.6	586.4	492.2	478.1
30°	310.1	303.1	337.9	290.0	270.2
32.5°	203.4	194.5	205.7	184.6	168.6
35°	136.1	138.9	130.3	129.3	109.2
37.5°	85.0	97.7	86.2	92.0	70.3
40°	54.9	70.9	61.0	67.4	51.7
42.5°	45.0	54.6	50.1	53.3	46.0
45°	35.8	44.4	44.4	44.4	36.1
47.5°	19.8	29.7	38.0	30.3	21.1
50°	11.2	15.0	29.4	15.6	11.8
52.5°	7.7	8.6	20.1	8.9	8.0
55°	5.7	6.1	10.9	6.4	6.1
57.5°	4.5	4.8	5.7	4.8	4.5
60°	3.5	3.5	4.2	3.8	3.5
62.5°	2.6	2.6	2.9	2.6	2.6
65°	1.9	1.9	1.9	1.9	1.9
67.5°	1.0	1.3	1.3	1.3	1.3
70°	1.0	0.6	0.6	0.6	1.0
72.5°	0.6	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)