

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789596

Luminaire Tested: LER6D15D010-EC6DR300215IC9040-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2711.4 lumens
Efficiency: N/A
Efficacy: 171.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789596

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789596

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	667351	667351	667351
5°	648194	647434	648225
10°	561433	557469	561301
15°	366303	364338	362508
20°	182143	188977	181899
25°	91753	103467	89870
30°	36733	40029	32004
35°	17044	16315	13680
40°	7354	8173	6924
45°	5185	6441	5239
50°	1786	4692	1881
55°	1028	1948	1081
60°	720	857	720
65°	471	471	471
70°	291	201	291
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 6441 cd/sqm



TEST NUMBER: P789596

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	766.7	28.3
10°-20°	1234.7	45.5
20°-30°	533.6	19.7
30°-40°	121.6	4.5
40°-50°	41.8	1.5
50°-60°	10.2	0.4
60°-70°	2.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2534.9	93.5
0°-40°	2656.6	98.0
0°-60°	2708.5	99.9
0°-90°	2711.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2711.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8719	8719	8719	8719	8719	
5°	8436	8428	8426	8444	8436	767
15°	4622	4567	4598	4583	4575	1238
25°	1086	1128	1225	1099	1064	520
35°	182	186	175	173	146	124
45°	48	60	60	60	48	34
55°	8	8	15	9	8	8
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P789596

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8718.6	8718.6	8718.6	8718.6	8718.6
2.5°	8660.8	8654.8	8658.2	8662.5	8664.2
5°	8436.1	8427.9	8426.2	8443.8	8436.5
7.5°	7982.7	7971.2	7953.6	7993.4	8030.7
10°	7223.4	7210.5	7172.4	7191.3	7221.7
12.5°	6102.3	6060.8	6059.9	6119.9	6111.7
15°	4622.5	4566.9	4597.7	4582.7	4574.6
17.5°	3108.5	3087.1	3128.2	3115.8	3062.3
20°	2236.1	2241.7	2320.0	2280.7	2233.1
22.5°	1631.7	1651.9	1744.7	1643.3	1606.1
25°	1086.4	1127.5	1225.1	1098.8	1064.1
27.5°	668.2	687.0	785.9	659.6	640.8
30°	415.6	406.2	452.9	388.7	362.1
32.5°	272.7	260.7	275.7	247.4	226.0
35°	182.4	186.2	174.6	173.4	146.4
37.5°	113.9	131.0	115.6	123.3	94.2
40°	73.6	95.0	81.8	90.3	69.3
42.5°	60.4	73.2	67.2	71.5	61.6
45°	47.9	59.5	59.5	59.5	48.4
47.5°	26.5	39.8	50.9	40.7	28.3
50°	15.0	20.1	39.4	21.0	15.8
52.5°	10.3	11.6	27.0	12.0	10.7
55°	7.7	8.1	14.6	8.6	8.1
57.5°	6.0	6.4	7.7	6.4	6.0
60°	4.7	4.7	5.6	5.1	4.7
62.5°	3.4	3.4	3.9	3.4	3.4
65°	2.6	2.6	2.6	2.6	2.6
67.5°	1.3	1.7	1.7	1.7	1.7
70°	1.3	0.9	0.9	0.9	1.3
72.5°	0.9	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)