

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789597

Luminaire Tested: LER6D15D010-EC6DR300215IC9040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR300215IC9040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2303.6 lumens
Efficiency: N/A
Efficacy: 145.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789597

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789597

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	566965	566965	566965
5°	550690	550044	550713
10°	476978	473612	476869
15°	311205	309533	307980
20°	154750	160557	154538
25°	77953	87902	76357
30°	31209	34010	27196
35°	14474	13867	11624
40°	6255	6944	5885
45°	4406	5467	4449
50°	1512	3989	1608
55°	867	1655	921
60°	612	720	612
65°	398	398	398
70°	246	157	246
75°	0	118	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 5467 cd/sqm



TEST NUMBER: P789597

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	651.3	28.3
10°-20°	1049.0	45.5
20°-30°	453.3	19.7
30°-40°	103.3	4.5
40°-50°	35.5	1.5
50°-60°	8.7	0.4
60°-70°	2.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2153.6	93.5
0°-40°	2257.0	98.0
0°-60°	2301.1	99.9
0°-90°	2303.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2303.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7407	7407	7407	7407	7407	
5°	7167	7160	7159	7174	7167	652
15°	3927	3880	3906	3893	3886	1052
25°	923	958	1041	934	904	442
35°	155	158	148	147	124	105
45°	41	50	50	50	41	29
55°	6	7	12	7	7	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P789597

CATALOG NUMBER: LER6D15D010-EC6DR300215IC9040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7407.1	7407.1	7407.1	7407.1	7407.1
2.5°	7358.0	7352.9	7355.8	7359.5	7360.9
5°	7167.1	7160.2	7158.7	7173.6	7167.4
7.5°	6782.0	6772.1	6757.2	6791.1	6822.7
10°	6136.8	6125.9	6093.5	6109.5	6135.4
12.5°	5184.4	5149.1	5148.4	5199.3	5192.4
15°	3927.2	3879.9	3906.1	3893.4	3886.5
17.5°	2640.9	2622.7	2657.7	2647.1	2601.6
20°	1899.8	1904.5	1971.1	1937.6	1897.2
22.5°	1386.3	1403.4	1482.3	1396.1	1364.5
25°	923.0	957.9	1040.8	933.5	904.1
27.5°	567.7	583.7	667.7	560.4	544.4
30°	353.1	345.1	384.8	330.2	307.7
32.5°	231.7	221.5	234.2	210.2	192.0
35°	154.9	158.2	148.4	147.3	124.4
37.5°	96.7	111.3	98.2	104.7	80.0
40°	62.6	80.7	69.5	76.7	58.9
42.5°	51.3	62.2	57.1	60.7	52.4
45°	40.7	50.5	50.5	50.5	41.1
47.5°	22.5	33.8	43.3	34.5	24.0
50°	12.7	17.1	33.5	17.8	13.5
52.5°	8.7	9.8	22.9	10.2	9.1
55°	6.5	6.9	12.4	7.3	6.9
57.5°	5.1	5.5	6.5	5.5	5.1
60°	4.0	4.0	4.7	4.4	4.0
62.5°	2.9	2.9	3.3	2.9	2.9
65°	2.2	2.2	2.2	2.2	2.2
67.5°	1.1	1.5	1.5	1.5	1.5
70°	1.1	0.7	0.7	0.7	1.1
72.5°	0.7	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)