

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789627

Luminaire Tested: LER6D15D010-EC6DR350215IC9030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR350215IC9030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2328.2 lumens
Efficiency: N/A
Efficacy: 147.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789627
CATALOG NUMBER: LER6D15D010-EC6DR350215IC9030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789627

CATALOG NUMBER: LER6D15D010-EC6DR350215IC9030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96											96																	
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92											92																	
3	106	101	97	94	105	100	96	94	97	95	92	95	93	91	93	91	89	88											88																	
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84											84																	
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81											81																	
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78											78																	
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75											75																	
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72											72																	
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70											70																	
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68											68																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	699935
5°	683481
10°	615996
15°	478115
20°	271183
25°	105498
30°	39363
35°	21568
40°	14106
45°	8576
50°	5456
55°	3867
60°	2819
65°	1525
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8576 cd/sqm



TEST NUMBER: P789627

CATALOG NUMBER: LER6D15D010-EC6DR350215IC9030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	573.1	24.6
10°-20°	1119.0	48.1
20°-30°	456.4	19.6
30°-40°	109.2	4.7
40°-50°	45.5	2.0
50°-60°	18.8	0.8
60°-70°	5.9	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2148.5	92.3
0°-40°	2257.7	97.0
0°-60°	2322.1	99.7
0°-90°	2328.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2328.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6406	
5°	6232	573
15°	4227	1119
25°	875	456
35°	162	109
45°	56	46
55°	20	19
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789627

CATALOG NUMBER: LER6D15D010-EC6DR350215IC9030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6406.1
2.5°	6367.6
5°	6231.7
7.5°	5960.6
10°	5552.2
12.5°	4977.2
15°	4226.8
17.5°	3309.1
20°	2332.3
22.5°	1487.2
25°	875.1
27.5°	494.7
30°	312.0
32.5°	219.0
35°	161.7
37.5°	125.1
40°	98.9
42.5°	76.2
45°	55.5
47.5°	41.6
50°	32.1
52.5°	25.5
55°	20.3
57.5°	16.4
60°	12.9
62.5°	9.4
65°	5.9
67.5°	2.1
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)