

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788331

Luminaire Tested: LER6D08D010-EC6DR300210IC9027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR300210IC9027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1266.5 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788331

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P788331

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	311715	311715	311715
5°	302764	302410	302779
10°	262241	260392	262179
15°	171103	170183	169328
20°	85081	88274	84967
25°	42853	48326	41983
30°	17155	18693	14946
35°	7961	7625	6391
40°	3437	3817	3237
45°	2425	3009	2446
50°	834	2191	881
55°	480	907	507
60°	337	398	337
65°	217	217	217
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 3009 cd/sqm



TEST NUMBER: P788331

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.1	28.3
10°-20°	576.7	45.5
20°-30°	249.2	19.7
30°-40°	56.8	4.5
40°-50°	19.5	1.5
50°-60°	4.8	0.4
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.1	93.5
0°-40°	1240.9	98.0
0°-60°	1265.1	99.9
0°-90°	1266.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1266.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4072	4072	4072	4072	4072	
5°	3940	3937	3936	3944	3941	358
15°	2159	2133	2148	2141	2137	578
25°	507	527	572	513	497	243
35°	85	87	82	81	68	58
45°	22	28	28	28	23	16
55°	4	4	7	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P788331

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4072.4	4072.4	4072.4	4072.4	4072.4
2.5°	4045.4	4042.6	4044.2	4046.2	4047.0
5°	3940.4	3936.6	3935.8	3944.0	3940.6
7.5°	3728.7	3723.3	3715.1	3733.7	3751.1
10°	3374.0	3368.0	3350.2	3359.0	3373.2
12.5°	2850.3	2831.0	2830.6	2858.5	2854.7
15°	2159.2	2133.2	2147.6	2140.6	2136.8
17.5°	1452.0	1442.0	1461.2	1455.4	1430.4
20°	1044.5	1047.1	1083.7	1065.3	1043.1
22.5°	762.2	771.6	815.0	767.6	750.2
25°	507.4	526.6	572.2	513.2	497.1
27.5°	312.1	320.9	367.1	308.1	299.3
30°	194.1	189.7	211.5	181.5	169.1
32.5°	127.4	121.8	128.8	115.6	105.6
35°	85.2	87.0	81.6	81.0	68.4
37.5°	53.2	61.2	54.0	57.6	44.0
40°	34.4	44.4	38.2	42.2	32.4
42.5°	28.2	34.2	31.4	33.4	28.8
45°	22.4	27.8	27.8	27.8	22.6
47.5°	12.4	18.6	23.8	19.0	13.2
50°	7.0	9.4	18.4	9.8	7.4
52.5°	4.8	5.4	12.6	5.6	5.0
55°	3.6	3.8	6.8	4.0	3.8
57.5°	2.8	3.0	3.6	3.0	2.8
60°	2.2	2.2	2.6	2.4	2.2
62.5°	1.6	1.6	1.8	1.6	1.6
65°	1.2	1.2	1.2	1.2	1.2
67.5°	0.6	0.8	0.8	0.8	0.8
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)