

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788338

Luminaire Tested: LER6D08D010-EC6DR300210IC9030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR300210IC9030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1182.0 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788338

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P788338

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	290926	290926	290926
5°	282571	282241	282587
10°	244754	243020	244691
15°	159684	158828	158027
20°	79403	82384	79297
25°	39999	45108	39179
30°	16015	17447	13956
35°	7429	7111	5962
40°	3207	3557	3018
45°	2262	2804	2284
50°	774	2048	822
55°	454	841	467
60°	321	367	321
65°	199	199	199
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2804 cd/sqm



TEST NUMBER: P788338

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.2	28.3
10°-20°	538.3	45.5
20°-30°	232.6	19.7
30°-40°	53.0	4.5
40°-50°	18.2	1.5
50°-60°	4.4	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.1	93.5
0°-40°	1158.1	98.0
0°-60°	1180.7	99.9
0°-90°	1182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1182.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3801	3801	3801	3801	3801	
5°	3678	3674	3673	3681	3678	334
15°	2015	1991	2004	1998	1994	540
25°	474	492	534	479	464	227
35°	80	81	76	76	64	54
45°	21	26	26	26	21	15
55°	3	4	6	4	4	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P788338

CATALOG NUMBER: LER6D08D010-EC6DR300210IC9030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3800.8	3800.8	3800.8	3800.8	3800.8
2.5°	3775.6	3773.0	3774.5	3776.3	3777.1
5°	3677.6	3674.1	3673.3	3681.0	3677.8
7.5°	3480.0	3475.0	3467.3	3484.7	3500.9
10°	3149.0	3143.4	3126.7	3135.0	3148.2
12.5°	2660.2	2642.1	2641.8	2667.9	2664.3
15°	2015.1	1990.9	2004.3	1997.8	1994.2
17.5°	1355.1	1345.8	1363.7	1358.3	1335.0
20°	974.8	977.2	1011.4	994.2	973.5
22.5°	711.3	720.1	760.6	716.4	700.1
25°	473.6	491.5	534.1	479.0	463.9
27.5°	291.3	299.5	342.6	287.6	279.3
30°	181.2	177.1	197.4	169.4	157.9
32.5°	118.9	113.6	120.2	107.9	98.5
35°	79.5	81.2	76.1	75.6	63.8
37.5°	49.6	57.1	50.4	53.7	41.1
40°	32.1	41.4	35.6	39.4	30.2
42.5°	26.3	31.9	29.3	31.2	26.9
45°	20.9	25.9	25.9	25.9	21.1
47.5°	11.6	17.4	22.2	17.7	12.3
50°	6.5	8.8	17.2	9.1	6.9
52.5°	4.5	5.0	11.8	5.2	4.7
55°	3.4	3.5	6.3	3.7	3.5
57.5°	2.6	2.8	3.4	2.8	2.6
60°	2.1	2.1	2.4	2.2	2.1
62.5°	1.5	1.5	1.7	1.5	1.5
65°	1.1	1.1	1.1	1.1	1.1
67.5°	0.6	0.7	0.7	0.7	0.7
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)