

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789845

Luminaire Tested: LER6D15D010-EC6DR600215IC9024-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR600215IC9024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1679.4 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789845
CATALOG NUMBER: LER6D15D010-EC6DR600215IC9024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P789845

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217921
5°	223272
10°	225975
15°	215269
20°	189804
25°	153516
30°	103845
35°	52033
40°	8444
45°	8267
50°	8431
55°	8553
60°	8785
65°	8997
70°	9200
75°	9330
80°	8998
85°	7522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 9330 cd/sqm



TEST NUMBER: P789845

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.6	11.6
10°-20°	526.4	31.3
20°-30°	566.4	33.7
30°-40°	246.2	14.7
40°-50°	41.4	2.5
50°-60°	40.2	2.4
60°-70°	34.4	2.0
70°-80°	23.0	1.4
80°-90°	6.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.3	76.7
0°-40°	1533.5	91.3
0°-60°	1615.1	96.2
0°-90°	1679.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1679.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1994	
5°	2036	195
15°	1903	526
25°	1273	566
35°	390	246
45°	54	41
55°	45	40
65°	35	34
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P789845

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1994.5
2.5°	2050.5
5°	2035.7
7.5°	2040.4
10°	2036.8
12.5°	1994.7
15°	1903.1
17.5°	1780.1
20°	1632.4
22.5°	1474.3
25°	1273.4
27.5°	1018.5
30°	823.1
32.5°	634.4
35°	390.1
37.5°	166.9
40°	59.2
42.5°	54.5
45°	53.5
47.5°	51.7
50°	49.6
52.5°	47.2
55°	44.9
57.5°	42.6
60°	40.2
62.5°	37.6
65°	34.8
67.5°	31.9
70°	28.8
72.5°	25.4
75°	22.1
77.5°	18.2
80°	14.3
82.5°	10.1
85°	6.0
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)