

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788542

Luminaire Tested: LER6D08D010-EC6DR500210IC9035-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR500210IC9035-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1485.9 lumens
Efficiency: N/A
Efficacy: 167.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788542
CATALOG NUMBER: LER6D08D010-EC6DR500210IC9035-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P788542

CATALOG NUMBER: LER6D08D010-EC6DR500210IC9035-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65	65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261581
5°	258840
10°	254577
15°	231818
20°	192897
25°	136927
30°	72481
35°	29531
40°	10968
45°	5022
50°	2057
55°	1086
60°	524
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5022 cd/sqm



TEST NUMBER: P788542

CATALOG NUMBER: LER6D08D010-EC6DR500210IC9035-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.1	15.0
10°-20°	563.7	37.9
20°-30°	506.4	34.1
30°-40°	158.5	10.7
40°-50°	27.8	1.9
50°-60°	5.5	0.4
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1293.2	87.0
0°-40°	1451.8	97.7
0°-60°	1485.1	99.9
0°-90°	1485.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1485.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2394	
5°	2360	223
15°	2049	564
25°	1136	506
35°	221	159
45°	32	28
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P788542

CATALOG NUMBER: LER6D08D010-EC6DR500210IC9035-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2394.1
2.5°	2382.2
5°	2360.0
7.5°	2326.1
10°	2294.6
12.5°	2193.7
15°	2049.4
17.5°	1866.1
20°	1659.0
22.5°	1419.4
25°	1135.8
27.5°	835.1
30°	574.5
32.5°	374.0
35°	221.4
37.5°	127.2
40°	76.9
42.5°	50.1
45°	32.5
47.5°	19.8
50°	12.1
52.5°	8.3
55°	5.7
57.5°	3.8
60°	2.4
62.5°	1.4
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)