

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789855

Luminaire Tested: LER6D15D010-EC6DR600215IC9027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR600215IC9027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2485.8 lumens
Efficiency: N/A
Efficacy: 157.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789855
CATALOG NUMBER: LER6D15D010-EC6DR600215IC9027-6LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P789855
CATALOG NUMBER: LER6D15D010-EC6DR600215IC9027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20	20		
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	322549
5°	330482
10°	334470
15°	318634
20°	280938
25°	227224
30°	153705
35°	77015
40°	12494
45°	12222
50°	12476
55°	12668
60°	13002
65°	13314
70°	13609
75°	13804
80°	13276
85°	11032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 13804 cd/sqm

TEST NUMBER: P789855

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.0	11.6
10°-20°	779.2	31.3
20°-30°	838.3	33.7
30°-40°	364.4	14.7
40°-50°	61.2	2.5
50°-60°	59.5	2.4
60°-70°	50.9	2.0
70°-80°	34.1	1.4
80°-90°	10.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1905.5	76.7
0°-40°	2269.9	91.3
0°-60°	2390.6	96.2
0°-90°	2485.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2485.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2952	
5°	3013	288
15°	2817	779
25°	1885	838
35°	577	364
45°	79	61
55°	66	60
65°	52	51
75°	33	34
85°	9	10
90°	0	



TEST NUMBER: P789855

CATALOG NUMBER: LER6D15D010-EC6DR600215IC9027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2952.1
2.5°	3035.1
5°	3013.2
7.5°	3020.1
10°	3014.7
12.5°	2952.5
15°	2816.9
17.5°	2634.8
20°	2416.2
22.5°	2182.2
25°	1884.8
27.5°	1507.6
30°	1218.3
32.5°	939.0
35°	577.4
37.5°	247.0
40°	87.6
42.5°	80.7
45°	79.1
47.5°	76.5
50°	73.4
52.5°	69.9
55°	66.5
57.5°	63.0
60°	59.5
62.5°	55.7
65°	51.5
67.5°	47.3
70°	42.6
72.5°	37.7
75°	32.7
77.5°	26.9
80°	21.1
82.5°	15.0
85°	8.8
87.5°	3.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)