

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789906

Luminaire Tested: LER6D15D010-EC6DR650215IC9027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D15D010-EC6DR650215IC9027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2069.0 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789906
CATALOG NUMBER: LER6D15D010-EC6DR650215IC9027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789906

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109718
5°	109439
10°	109346
15°	105975
20°	96479
25°	84077
30°	69927
35°	55406
40°	39988
45°	25266
50°	13166
55°	6995
60°	3679
65°	2018
70°	854
75°	925
80°	639
85°	536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25266 cd/sqm



TEST NUMBER: P789906

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.7	8.6
10°-20°	486.5	23.5
20°-30°	594.7	28.7
30°-40°	482.5	23.3
40°-50°	240.4	11.6
50°-60°	67.1	3.2
60°-70°	15.2	0.7
70°-80°	4.0	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.8	60.8
0°-40°	1741.3	84.2
0°-60°	2048.8	99.0
0°-90°	2069.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2069.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1879	
5°	1867	178
15°	1753	486
25°	1305	595
35°	777	482
45°	306	240
55°	69	67
65°	15	15
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P789906

CATALOG NUMBER: LER6D15D010-EC6DR650215IC9027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1878.6
2.5°	1877.2
5°	1866.7
7.5°	1860.7
10°	1843.8
12.5°	1809.6
15°	1752.7
17.5°	1663.8
20°	1552.3
22.5°	1431.9
25°	1304.7
27.5°	1168.6
30°	1036.9
32.5°	906.9
35°	777.1
37.5°	647.6
40°	524.5
42.5°	409.1
45°	305.9
47.5°	213.1
50°	144.9
52.5°	99.9
55°	68.7
57.5°	46.4
60°	31.5
62.5°	21.8
65°	14.6
67.5°	7.5
70°	5.0
72.5°	4.7
75°	4.1
77.5°	2.8
80°	1.9
82.5°	1.4
85°	0.8
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)