

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789940

Luminaire Tested: LER6D15D010-EC6DR700215IC9024-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789940  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR700215IC9024-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1676.7 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P789940

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9024-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P789940

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9024-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	205967
5°	199844
10°	194278
15°	191730
20°	179037
25°	134492
30°	95077
35°	33679
40°	17715
45°	18867
50°	19531
55°	19906
60°	20017
65°	19597
70°	18497
75°	17139
80°	15227
85°	12286

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 20030 cd/sqm



TEST NUMBER: P789940

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9024-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.9	10.3
10°-20°	471.4	28.1
20°-30°	519.2	31.0
30°-40°	198.4	11.8
40°-50°	93.7	5.6
50°-60°	93.1	5.6
60°-70°	74.6	4.4
70°-80°	42.8	2.6
80°-90°	11.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1162.5	69.3
0°-40°	1360.9	81.2
0°-60°	1547.7	92.3
0°-90°	1676.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1676.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1885	
5°	1822	172
15°	1695	471
25°	1116	519
35°	252	198
45°	122	94
55°	104	93
65°	76	75
75°	41	43
85°	10	12
90°	0	



TEST NUMBER: P789940

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9024-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1885.1
2.5°	1865.4
5°	1822.1
7.5°	1786.0
10°	1751.1
12.5°	1721.5
15°	1695.0
17.5°	1630.8
20°	1539.8
22.5°	1343.4
25°	1115.6
27.5°	971.2
30°	753.6
32.5°	486.8
35°	252.5
37.5°	136.4
40°	124.2
42.5°	123.3
45°	122.1
47.5°	119.4
50°	114.9
52.5°	109.8
55°	104.5
57.5°	98.5
60°	91.6
62.5°	83.9
65°	75.8
67.5°	66.9
70°	57.9
72.5°	48.9
75°	40.6
77.5°	31.9
80°	24.2
82.5°	17.0
85°	9.8
87.5°	3.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)