

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789956

Luminaire Tested: LER6D15D010-EC6DR700215IC9030-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789956  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D15D010-EC6DR700215IC9030-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1921.8 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789956  
CATALOG NUMBER: LER6D15D010-EC6DR700215IC9030-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P789956

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9030-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	236080
5°	229063
10°	222680
15°	219760
20°	205210
25°	154167
30°	108980
35°	38601
40°	20296
45°	21617
50°	22386
55°	22802
60°	22945
65°	22467
70°	21212
75°	19630
80°	17429
85°	14166

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 22958 cd/sqm



TEST NUMBER: P789956

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9030-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.0	10.3
10°-20°	540.3	28.1
20°-30°	595.1	31.0
30°-40°	227.4	11.8
40°-50°	107.3	5.6
50°-60°	106.7	5.6
60°-70°	85.4	4.4
70°-80°	49.1	2.6
80°-90°	13.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1332.4	69.3
0°-40°	1559.8	81.2
0°-60°	1773.9	92.3
0°-90°	1921.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1921.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2161	
5°	2088	197
15°	1943	540
25°	1279	595
35°	289	227
45°	140	107
55°	120	107
65°	87	85
75°	46	49
85°	11	13
90°	0	



TEST NUMBER: P789956

CATALOG NUMBER: LER6D15D010-EC6DR700215IC9030-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2160.7
2.5°	2138.1
5°	2088.5
7.5°	2047.1
10°	2007.1
12.5°	1973.2
15°	1942.8
17.5°	1869.2
20°	1764.9
22.5°	1539.8
25°	1278.8
27.5°	1113.2
30°	863.8
32.5°	558.0
35°	289.4
37.5°	156.3
40°	142.3
42.5°	141.3
45°	139.9
47.5°	136.8
50°	131.7
52.5°	125.9
55°	119.7
57.5°	112.9
60°	105.0
62.5°	96.1
65°	86.9
67.5°	76.6
70°	66.4
72.5°	56.1
75°	46.5
77.5°	36.6
80°	27.7
82.5°	19.5
85°	11.3
87.5°	4.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)