

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788722

Luminaire Tested: LER6D08D010-EC6DR700210IC9030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR700210IC9030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1069.9 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788722

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P788722

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131419
5°	127512
10°	123960
15°	122334
20°	114238
25°	85824
30°	60672
35°	21488
40°	11296
45°	12037
50°	12460
55°	12706
60°	12784
65°	12513
70°	11788
75°	10934
80°	9690
85°	7898

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 12784 cd/sqm



TEST NUMBER: P788722

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.7	10.2
10°-20°	300.8	28.1
20°-30°	331.3	31.0
30°-40°	126.6	11.8
40°-50°	59.8	5.6
50°-60°	59.4	5.6
60°-70°	47.6	4.4
70°-80°	27.3	2.6
80°-90°	7.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	741.8	69.3
0°-40°	868.3	81.2
0°-60°	987.5	92.3
0°-90°	1069.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1069.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1203	
5°	1163	110
15°	1082	301
25°	712	331
35°	161	127
45°	78	60
55°	67	59
65°	48	48
75°	26	27
85°	6	7
90°	0	



TEST NUMBER: P788722

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1202.8
2.5°	1190.2
5°	1162.6
7.5°	1139.6
10°	1117.3
12.5°	1098.4
15°	1081.5
17.5°	1040.6
20°	982.5
22.5°	857.2
25°	711.9
27.5°	619.7
30°	480.9
32.5°	310.6
35°	161.1
37.5°	87.0
40°	79.2
42.5°	78.7
45°	77.9
47.5°	76.2
50°	73.3
52.5°	70.1
55°	66.7
57.5°	62.8
60°	58.5
62.5°	53.5
65°	48.4
67.5°	42.7
70°	36.9
72.5°	31.2
75°	25.9
77.5°	20.4
80°	15.4
82.5°	10.9
85°	6.3
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)