

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788728

Luminaire Tested: LER6D08D010-EC6DR700210IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P788728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D08D010-EC6DR700210IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1445.9 lumens
Efficiency: N/A
Efficacy: 162.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P788728

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P788728

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177614
5°	172337
10°	167540
15°	165340
20°	154387
25°	115987
30°	81994
35°	29037
40°	15276
45°	16271
50°	16845
55°	17163
60°	17263
65°	16908
70°	15941
75°	14775
80°	13088
85°	10656

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 17265 cd/sqm



TEST NUMBER: P788728

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.2	10.3
10°-20°	406.5	28.1
20°-30°	447.7	31.0
30°-40°	171.1	11.8
40°-50°	80.8	5.6
50°-60°	80.3	5.6
60°-70°	64.3	4.4
70°-80°	36.9	2.6
80°-90°	10.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.5	69.3
0°-40°	1173.5	81.2
0°-60°	1334.6	92.3
0°-90°	1445.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1445.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1626	
5°	1571	148
15°	1462	407
25°	962	448
35°	218	171
45°	105	81
55°	90	80
65°	65	64
75°	35	37
85°	8	10
90°	0	



TEST NUMBER: P788728

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1625.6
2.5°	1608.6
5°	1571.3
7.5°	1540.2
10°	1510.1
12.5°	1484.6
15°	1461.7
17.5°	1406.3
20°	1327.8
22.5°	1158.5
25°	962.1
27.5°	837.5
30°	649.9
32.5°	419.8
35°	217.7
37.5°	117.6
40°	107.1
42.5°	106.3
45°	105.3
47.5°	103.0
50°	99.1
52.5°	94.7
55°	90.1
57.5°	84.9
60°	79.0
62.5°	72.3
65°	65.4
67.5°	57.7
70°	49.9
72.5°	42.2
75°	35.0
77.5°	27.5
80°	20.8
82.5°	14.7
85°	8.5
87.5°	3.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)