

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788745

Luminaire Tested: LER6D08D010-EC6DR700210IC9050-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P788745  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D08D010-EC6DR700210IC9050-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1541.8 lumens  
Efficiency: N/A  
Efficacy: 173.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P788745

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9050-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P788745  
 CATALOG NUMBER: LER6D08D010-EC6DR700210IC9050-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	189393
5°	183766
10°	178646
15°	176301
20°	164631
25°	123678
30°	87431
35°	30971
40°	16288
45°	17352
50°	17967
55°	18306
60°	18421
65°	18020
70°	16995
75°	15746
80°	13968
85°	11408

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 18424 cd/sqm



TEST NUMBER: P788745

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9050-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.0	10.2
10°-20°	433.5	28.1
20°-30°	477.4	31.0
30°-40°	182.4	11.8
40°-50°	86.1	5.6
50°-60°	85.7	5.6
60°-70°	68.6	4.4
70°-80°	39.4	2.6
80°-90°	10.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1069.0	69.3
0°-40°	1251.4	81.2
0°-60°	1423.2	92.3
0°-90°	1541.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1733	
5°	1676	158
15°	1559	433
25°	1026	477
35°	232	182
45°	112	86
55°	96	86
65°	70	69
75°	37	39
85°	9	11
90°	0	



TEST NUMBER: P788745

CATALOG NUMBER: LER6D08D010-EC6DR700210IC9050-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1733.4
2.5°	1715.3
5°	1675.5
7.5°	1642.3
10°	1610.2
12.5°	1583.0
15°	1558.6
17.5°	1499.6
20°	1415.9
22.5°	1235.3
25°	1025.9
27.5°	893.1
30°	693.0
32.5°	447.6
35°	232.2
37.5°	125.4
40°	114.2
42.5°	113.3
45°	112.3
47.5°	109.8
50°	105.7
52.5°	101.0
55°	96.1
57.5°	90.6
60°	84.3
62.5°	77.1
65°	69.7
67.5°	61.5
70°	53.2
72.5°	45.0
75°	37.3
77.5°	29.4
80°	22.2
82.5°	15.6
85°	9.1
87.5°	3.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)