

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788769

Luminaire Tested: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR100210IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1080.3 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788769
CATALOG NUMBER: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P788769

CATALOG NUMBER: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98																			
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97																			
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95																			
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94																			
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93																			
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91																			
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90																			
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89																			
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88																			
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2570021
5°	1218699
10°	249940
15°	68616
20°	27650
25°	14816
30°	8768
35°	5709
40°	3808
45°	2472
50°	1360
55°	1010
60°	590
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2472 cd/sqm



TEST NUMBER: P788769

CATALOG NUMBER: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	768.2	71.1
10°-20°	207.9	19.2
20°-30°	59.5	5.5
30°-40°	27.2	2.5
40°-50°	12.5	1.2
50°-60°	4.1	0.4
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1035.5	95.9
0°-40°	1062.7	98.4
0°-60°	1079.3	99.9
0°-90°	1080.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1080.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23522	
5°	11112	768
15°	607	208
25°	123	60
35°	43	27
45°	16	12
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P788769

CATALOG NUMBER: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23521.9
0.5°	23318.8
1°	22797.7
1.5°	21792.9
2°	20667.9
2.5°	19182.1
3°	17530.6
3.5°	15932.5
4°	14208.8
4.5°	12621.5
5°	11111.6
5.5°	9743.4
6°	8439.3
6.5°	7292.8
7°	6213.2
7.5°	5291.2
8°	4473.5
8.5°	3757.3
9°	3137.3
9.5°	2664.3
10°	2252.8
12.5°	1074.3
15°	606.6
17.5°	368.8
20°	237.8
22.5°	165.7
25°	122.9
27.5°	90.9
30°	69.5
32.5°	53.4
35°	42.8
37.5°	32.1
40°	26.7
42.5°	21.4
45°	16.0
47.5°	10.7
50°	8.0
52.5°	5.3
55°	5.3
57.5°	2.7
60°	2.7
62.5°	2.7
65°	0.0



TEST NUMBER: P788769
CATALOG NUMBER: LER6D10D010-EC6DR100210IC9030-6LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)