

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788831

Luminaire Tested: LER6D10D010-EC6DR150210IC9040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR150210IC9040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1064.2 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788831
CATALOG NUMBER: LER6D10D010-EC6DR150210IC9040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P788831

CATALOG NUMBER: LER6D10D010-EC6DR150210IC9040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1631460	1631460	1631460
5°	958726	946318	953797
10°	286137	288143	292547
15°	71170	72560	70319
20°	21298	24661	21749
25°	7510	9566	7603
30°	2756	3632	2801
35°	1380	1561	1336
40°	873	959	873
45°	644	686	644
50°	515	515	515
55°	425	425	425
60°	344	344	344
65°	264	264	264
70°	227	227	227
75°	136	136	189
80°	95	95	95
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 686 cd/sqm



TEST NUMBER: P788831

CATALOG NUMBER: LER6D10D010-EC6DR150210IC9040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	690.2	64.9
10°-20°	283.9	26.7
20°-30°	56.4	5.3
30°-40°	14.1	1.3
40°-50°	7.4	0.7
50°-60°	5.5	0.5
60°-70°	3.9	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1030.5	96.8
0°-40°	1044.6	98.2
0°-60°	1057.4	99.4
0°-90°	1064.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14499	14499	14499	14499	14499	
5°	9434	9337	9312	9376	9385	689
15°	819	835	835	821	810	281
25°	96	109	123	109	98	51
35°	19	20	22	20	18	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P788831

CATALOG NUMBER: LER6D10D010-EC6DR150210IC9040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14499.3	14499.3	14499.3	14499.3	14499.3
2.5°	13079.0	13090.0	13094.3	13107.2	13155.1
5°	9433.6	9336.6	9311.5	9375.9	9385.1
7.5°	5588.1	5607.7	5679.6	5695.5	5637.8
10°	3066.6	3091.7	3088.1	3110.2	3135.3
12.5°	1568.3	1548.6	1542.5	1567.7	1532.7
15°	819.4	834.8	835.4	820.7	809.6
17.5°	440.7	458.5	488.0	464.0	427.2
20°	260.3	276.2	301.4	281.7	265.8
22.5°	160.8	173.7	191.5	176.2	163.3
25°	96.4	109.3	122.8	108.6	97.6
27.5°	57.1	68.1	76.7	67.5	56.5
30°	36.8	43.0	48.5	42.4	37.4
32.5°	25.8	28.2	30.7	28.2	25.8
35°	19.0	20.3	21.5	20.3	18.4
37.5°	14.7	16.0	16.6	15.3	14.1
40°	12.3	12.9	13.5	12.9	12.3
42.5°	10.4	11.0	11.0	11.0	10.4
45°	9.2	9.2	9.8	9.2	9.2
47.5°	8.0	8.0	8.6	8.0	8.0
50°	7.4	7.4	7.4	7.4	7.4
52.5°	6.8	6.8	6.8	6.8	6.8
55°	6.1	6.1	6.1	6.1	6.1
57.5°	5.5	5.5	5.5	5.5	5.5
60°	4.9	4.9	4.9	4.9	4.9
62.5°	4.3	4.3	4.3	4.3	4.3
65°	3.7	3.7	3.7	3.7	3.7
67.5°	3.7	3.7	3.7	3.7	3.7
70°	3.1	3.1	3.1	3.1	3.1
72.5°	2.5	2.5	2.5	2.5	2.5
75°	1.8	1.8	1.8	1.8	2.5
77.5°	1.8	1.8	1.8	1.8	1.8
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)