

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790101

Luminaire Tested: LER6D20D010-EC6DR2015309030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR2015309030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2246.1 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790101

CATALOG NUMBER: LER6D20D010-EC6DR2015309030-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790101
 CATALOG NUMBER: LER6D20D010-EC6DR2015309030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1396800
5°	1260169
10°	707283
15°	359525
20°	152213
25°	70272
30°	37193
35°	20047
40°	10711
45°	6335
50°	3672
55°	1943
60°	1246
65°	879
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6335 cd/sqm



TEST NUMBER: P790101

CATALOG NUMBER: LER6D20D010-EC6DR2015309030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	910.2	40.5
10°-20°	896.3	39.9
20°-30°	292.8	13.0
30°-40°	99.7	4.4
40°-50°	33.5	1.5
50°-60°	10.1	0.4
60°-70°	3.4	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2099.3	93.5
0°-40°	2198.9	97.9
0°-60°	2242.5	99.8
0°-90°	2246.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2246.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12784	
5°	11490	910
15°	3178	896
25°	583	293
35°	150	100
45°	41	34
55°	10	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790101

CATALOG NUMBER: LER6D20D010-EC6DR2015309030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	12784.1
0.5°	12784.1
1°	12768.1
1.5°	12736.3
2°	12678.2
2.5°	12600.8
3°	12491.5
3.5°	12339.0
4°	12112.4
4.5°	11836.9
5°	11489.7
5.5°	11033.2
6°	10565.4
6.5°	10029.2
7°	9504.4
7.5°	8889.7
8°	8341.0
8.5°	7788.8
9°	7278.8
9.5°	6811.0
10°	6375.0
12.5°	4577.5
15°	3178.4
17.5°	2076.4
20°	1309.1
22.5°	848.1
25°	582.9
27.5°	409.8
30°	294.8
32.5°	211.7
35°	150.3
37.5°	104.7
40°	75.1
42.5°	54.6
45°	41.0
47.5°	31.9
50°	21.6
52.5°	13.7
55°	10.2
57.5°	8.0
60°	5.7
62.5°	4.6
65°	3.4



TEST NUMBER: P790101
CATALOG NUMBER: LER6D20D010-EC6DR2015309030-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.3
70°		1.1

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)