

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P788868

Luminaire Tested: LER6D10D010-EC6DR200210IC9030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P788868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR200210IC9030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1159.4 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P788868
CATALOG NUMBER: LER6D10D010-EC6DR200210IC9030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P788868

CATALOG NUMBER: LER6D10D010-EC6DR200210IC9030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	94		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	91		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	88	88		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	87	86	85	85	85		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	84	83	82	82	82		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	82	81	80	80	80		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	80	79	78	78	78		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	78	77	77	77	77		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	76	75	75	75	75		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	74	73	73	73	73		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	720968
5°	650446
10°	365069
15°	185565
20°	78566
25°	36263
30°	19202
35°	10351
40°	5534
45°	3276
50°	1904
55°	1010
60°	634
65°	465
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3276 cd/sqm



TEST NUMBER: P788868

CATALOG NUMBER: LER6D10D010-EC6DR200210IC9030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.8	40.5
10°-20°	462.6	39.9
20°-30°	151.1	13.0
30°-40°	51.5	4.4
40°-50°	17.3	1.5
50°-60°	5.2	0.5
60°-70°	1.8	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1083.5	93.5
0°-40°	1135.0	97.9
0°-60°	1157.6	99.8
0°-90°	1159.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6599	
5°	5930	470
15°	1640	463
25°	301	151
35°	78	51
45°	21	17
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P788868

CATALOG NUMBER: LER6D10D010-EC6DR200210IC9030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6598.6
0.5°	6598.6
1°	6590.4
1.5°	6573.9
2°	6544.0
2.5°	6504.0
3°	6447.6
3.5°	6368.9
4°	6251.9
4.5°	6109.7
5°	5930.5
5.5°	5694.9
6°	5453.4
6.5°	5176.6
7°	4905.8
7.5°	4588.5
8°	4305.2
8.5°	4020.3
9°	3757.0
9.5°	3515.5
10°	3290.5
12.5°	2362.7
15°	1640.5
17.5°	1071.8
20°	675.7
22.5°	437.8
25°	300.8
27.5°	211.5
30°	152.2
32.5°	109.3
35°	77.6
37.5°	54.1
40°	38.8
42.5°	28.2
45°	21.2
47.5°	16.5
50°	11.2
52.5°	7.1
55°	5.3
57.5°	4.1
60°	2.9
62.5°	2.4
65°	1.8



TEST NUMBER: P788868
CATALOG NUMBER: LER6D10D010-EC6DR200210IC9030-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.2
70°		0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)