

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790240

Luminaire Tested: LER6D20D010-EC6DR3520359030-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR3520359030-6LB DP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3197.0 lumens
Efficiency: N/A
Efficacy: 138.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790240

CATALOG NUMBER: LER6D20D010-EC6DR3520359030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P790240

CATALOG NUMBER: LER6D20D010-EC6DR3520359030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 103 | 101 | 100 | 99 | 98 | 98 | 96 | 96 | 96 | 96 |
| 2 | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 99 | 102 | 99 | 97 | 99 | 97 | 95 | 96 | 95 | 93 | 92 | 92 | 92 | 92 |
| 3 | 106 | 101 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 95 | 92 | 95 | 93 | 91 | 93 | 91 | 89 | 88 | 88 | 88 | 88 |
| 4 | 103 | 97 | 92 | 89 | 101 | 96 | 92 | 89 | 94 | 90 | 88 | 92 | 89 | 87 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 5 | 99 | 93 | 88 | 85 | 98 | 92 | 87 | 84 | 90 | 86 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 81 | 81 | 81 | 81 |
| 6 | 96 | 89 | 84 | 81 | 94 | 88 | 84 | 81 | 87 | 83 | 80 | 85 | 82 | 80 | 84 | 81 | 79 | 78 | 78 | 78 | 78 |
| 7 | 93 | 85 | 81 | 78 | 91 | 85 | 80 | 77 | 84 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 76 | 75 | 75 | 75 | 75 |
| 8 | 90 | 82 | 78 | 74 | 88 | 82 | 77 | 74 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 9 | 87 | 79 | 75 | 72 | 86 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | 70 | 70 | 70 |
| 10 | 84 | 77 | 72 | 69 | 83 | 76 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 69 | 74 | 71 | 69 | 68 | 68 | 68 | 68 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 961112 |
| 5° | 938527 |
| 10° | 845866 |
| 15° | 656531 |
| 20° | 372375 |
| 25° | 144872 |
| 30° | 54048 |
| 35° | 29624 |
| 40° | 19369 |
| 45° | 11790 |
| 50° | 7496 |
| 55° | 5296 |
| 60° | 3868 |
| 65° | 2120 |
| 70° | 160 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11790 cd/sqm



TEST NUMBER: P790240

CATALOG NUMBER: LER6D20D010-EC6DR3520359030-6LBDP1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 787.0 | 24.6 |
| 10°-20° | 1536.6 | 48.1 |
| 20°-30° | 626.7 | 19.6 |
| 30°-40° | 150.0 | 4.7 |
| 40°-50° | 62.5 | 2.0 |
| 50°-60° | 25.8 | 0.8 |
| 60°-70° | 8.1 | 0.3 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2950.3 | 92.3 |
| 0°-40° | 3100.2 | 97.0 |
| 0°-60° | 3188.6 | 99.7 |
| 0°-90° | 3197.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3197.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 8796 | |
| 5° | 8557 | 787 |
| 15° | 5804 | 1537 |
| 25° | 1202 | 627 |
| 35° | 222 | 150 |
| 45° | 76 | 63 |
| 55° | 28 | 26 |
| 65° | 8 | 8 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P790240

CATALOG NUMBER: LER6D20D010-EC6DR3520359030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 8796.5 |
| 2.5° | 8743.8 |
| 5° | 8557.1 |
| 7.5° | 8184.9 |
| 10° | 7624.1 |
| 12.5° | 6834.5 |
| 15° | 5804.1 |
| 17.5° | 4543.9 |
| 20° | 3202.6 |
| 22.5° | 2042.1 |
| 25° | 1201.7 |
| 27.5° | 679.3 |
| 30° | 428.4 |
| 32.5° | 300.8 |
| 35° | 222.1 |
| 37.5° | 171.7 |
| 40° | 135.8 |
| 42.5° | 104.6 |
| 45° | 76.3 |
| 47.5° | 57.1 |
| 50° | 44.1 |
| 52.5° | 35.0 |
| 55° | 27.8 |
| 57.5° | 22.5 |
| 60° | 17.7 |
| 62.5° | 13.0 |
| 65° | 8.2 |
| 67.5° | 2.9 |
| 70° | 0.5 |
| 72.5° | 0.5 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.5 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)