

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790341

Luminaire Tested: LER6D20D010-EC6DR4520359030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR4520359030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3788.9 lumens
Efficiency: N/A
Efficacy: 164.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790341
CATALOG NUMBER: LER6D20D010-EC6DR4520359030-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790341

CATALOG NUMBER: LER6D20D010-EC6DR4520359030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95																			
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77																			
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73																			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																			
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66																			
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63																			
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	731730
5°	710890
10°	680134
15°	622461
20°	493834
25°	308310
30°	169930
35°	76295
40°	30052
45°	14169
50°	6714
55°	3505
60°	1726
65°	414
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14169 cd/sqm



TEST NUMBER: P790341

CATALOG NUMBER: LER6D20D010-EC6DR4520359030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.0	16.1
10°-20°	1498.9	39.6
20°-30°	1186.9	31.3
30°-40°	395.2	10.4
40°-50°	78.4	2.1
50°-60°	17.8	0.5
60°-70°	2.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3294.8	87.0
0°-40°	3690.1	97.4
0°-60°	3786.3	99.9
0°-90°	3788.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3788.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6697	
5°	6482	609
15°	5503	1499
25°	2557	1187
35°	572	395
45°	92	78
55°	18	18
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790341

CATALOG NUMBER: LER6D20D010-EC6DR4520359030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6697.1
2.5°	6653.4
5°	6481.6
7.5°	6339.9
10°	6130.3
12.5°	5851.1
15°	5502.9
17.5°	4979.4
20°	4247.2
22.5°	3374.9
25°	2557.4
27.5°	1872.6
30°	1346.9
32.5°	916.0
35°	572.0
37.5°	339.2
40°	210.7
42.5°	138.5
45°	91.7
47.5°	59.0
50°	39.5
52.5°	26.3
55°	18.4
57.5°	12.1
60°	7.9
62.5°	4.2
65°	1.6
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)