

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789154

Luminaire Tested: LER6D10D010-EC6DR500210IC9030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P789154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR500210IC9030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1789.7 lumens
Efficiency: N/A
Efficacy: 153.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789154

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P789154

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	100														
	1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	97	95														
	2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	91	90														
	3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	86	85														
	4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	82	80														
	5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	77	76														
	6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	74	74	74	74	72														
	7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	70	69														
	8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	66	65														
	9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	63	63	63	63	62														
	10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	60	60	60	60	59														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315086
5°	311782
10°	306644
15°	279225
20°	232348
25°	164933
30°	87305
35°	35573
40°	13208
45°	6042
50°	2482
55°	1295
60°	634
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6042 cd/sqm



TEST NUMBER: P789154

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.7	15.0
10°-20°	679.0	37.9
20°-30°	610.0	34.1
30°-40°	191.0	10.7
40°-50°	33.4	1.9
50°-60°	6.7	0.4
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.7	87.0
0°-40°	1748.7	97.7
0°-60°	1788.7	99.9
0°-90°	1789.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1789.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2884	
5°	2843	269
15°	2468	679
25°	1368	610
35°	267	191
45°	39	33
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789154

CATALOG NUMBER: LER6D10D010-EC6DR500210IC9030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2883.8
2.5°	2869.4
5°	2842.7
7.5°	2801.8
10°	2763.9
12.5°	2642.4
15°	2468.5
17.5°	2247.7
20°	1998.3
22.5°	1709.7
25°	1368.1
27.5°	1005.8
30°	692.0
32.5°	450.5
35°	266.7
37.5°	153.2
40°	92.6
42.5°	60.3
45°	39.1
47.5°	23.8
50°	14.6
52.5°	10.0
55°	6.8
57.5°	4.6
60°	2.9
62.5°	1.7
65°	0.7
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)