

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790399

Luminaire Tested: LER6D20D010-EC6DR5020359040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR5020359040-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3358.9 lumens
Efficiency: N/A
Efficacy: 145.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790399

CATALOG NUMBER: LER6D20D010-EC6DR5020359040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P790399

CATALOG NUMBER: LER6D20D010-EC6DR5020359040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95					95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90					90			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85					85			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80					80			
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76					76			
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72					72			
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69					69			
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65					65			
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62					62			
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59					59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	591319
5°	585122
10°	575489
15°	524028
20°	436047
25°	309527
30°	163836
35°	66758
40°	24789
45°	11357
50°	4657
55°	2438
60°	1202
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11357 cd/sqm



TEST NUMBER: P790399

CATALOG NUMBER: LER6D20D010-EC6DR5020359040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.3	15.0
10°-20°	1274.4	37.9
20°-30°	1144.7	34.1
30°-40°	358.4	10.7
40°-50°	62.8	1.9
50°-60°	12.5	0.4
60°-70°	1.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2923.3	87.0
0°-40°	3281.7	97.7
0°-60°	3357.0	99.9
0°-90°	3358.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3358.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5412	
5°	5335	504
15°	4633	1274
25°	2568	1145
35°	500	358
45°	74	63
55°	13	13
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790399

CATALOG NUMBER: LER6D20D010-EC6DR5020359040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5412.0
2.5°	5385.1
5°	5334.9
7.5°	5258.2
10°	5187.1
12.5°	4958.9
15°	4632.7
17.5°	4218.4
20°	3750.2
22.5°	3208.6
25°	2567.5
27.5°	1887.7
30°	1298.6
32.5°	845.5
35°	500.5
37.5°	287.5
40°	173.8
42.5°	113.2
45°	73.5
47.5°	44.7
50°	27.4
52.5°	18.7
55°	12.8
57.5°	8.7
60°	5.5
62.5°	3.2
65°	1.4
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)