

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789232

Luminaire Tested: LER6D10D010-EC6DR600210IC9024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR600210IC9024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1587.1 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789232

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789232

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205946
5°	211010
10°	213549
15°	203437
20°	179374
25°	145077
30°	98130
35°	49178
40°	7973
45°	7803
50°	7972
55°	8077
60°	8304
65°	8506
70°	8689
75°	8823
80°	8494
85°	7020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 8823 cd/sqm



TEST NUMBER: P789232

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	11.6
10°-20°	497.5	31.3
20°-30°	535.2	33.7
30°-40°	232.7	14.7
40°-50°	39.1	2.5
50°-60°	38.0	2.4
60°-70°	32.5	2.0
70°-80°	21.8	1.4
80°-90°	6.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1216.6	76.7
0°-40°	1449.2	91.3
0°-60°	1526.3	96.2
0°-90°	1587.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1587.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1885	
5°	1924	184
15°	1798	497
25°	1203	535
35°	369	233
45°	50	39
55°	42	38
65°	33	33
75°	21	22
85°	6	7
90°	0	



TEST NUMBER: P789232

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1884.9
2.5°	1937.8
5°	1923.9
7.5°	1928.3
10°	1924.8
12.5°	1885.1
15°	1798.5
17.5°	1682.2
20°	1542.7
22.5°	1393.3
25°	1203.4
27.5°	962.5
30°	777.8
32.5°	599.5
35°	368.7
37.5°	157.7
40°	55.9
42.5°	51.5
45°	50.5
47.5°	48.8
50°	46.9
52.5°	44.6
55°	42.4
57.5°	40.2
60°	38.0
62.5°	35.6
65°	32.9
67.5°	30.2
70°	27.2
72.5°	24.0
75°	20.9
77.5°	17.2
80°	13.5
82.5°	9.6
85°	5.6
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)