

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789233

Luminaire Tested: LER6D10D010-EC6DR600210IC9024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR600210IC9024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1666.4 lumens
Efficiency: N/A
Efficacy: 142.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789233

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789233

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216238
5°	221561
10°	224234
15°	213606
20°	188339
25°	152334
30°	103038
35°	51632
40°	8372
45°	8205
50°	8363
55°	8496
60°	8719
65°	8919
70°	9136
75°	9245
80°	8935
85°	7396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 9245 cd/sqm



TEST NUMBER: P789233

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.1	11.6
10°-20°	522.4	31.3
20°-30°	562.0	33.7
30°-40°	244.3	14.7
40°-50°	41.0	2.5
50°-60°	39.9	2.4
60°-70°	34.1	2.0
70°-80°	22.8	1.4
80°-90°	6.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1277.4	76.7
0°-40°	1521.7	91.3
0°-60°	1602.7	96.2
0°-90°	1666.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1666.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1979	
5°	2020	193
15°	1888	522
25°	1264	562
35°	387	244
45°	53	41
55°	45	40
65°	34	34
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P789233

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1979.1
2.5°	2034.7
5°	2020.1
7.5°	2024.7
10°	2021.1
12.5°	1979.4
15°	1888.4
17.5°	1766.4
20°	1619.8
22.5°	1463.0
25°	1263.6
27.5°	1010.7
30°	816.7
32.5°	629.5
35°	387.1
37.5°	165.6
40°	58.7
42.5°	54.1
45°	53.1
47.5°	51.3
50°	49.2
52.5°	46.9
55°	44.6
57.5°	42.2
60°	39.9
62.5°	37.3
65°	34.5
67.5°	31.7
70°	28.6
72.5°	25.2
75°	21.9
77.5°	18.0
80°	14.2
82.5°	10.0
85°	5.9
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)