

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789257

Luminaire Tested: LER6D10D010-EC6DR600210IC9035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR600210IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2016.4 lumens
Efficiency: N/A
Efficacy: 172.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P789257
CATALOG NUMBER: LER6D10D010-EC6DR600210IC9035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789257

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261658
5°	268086
10°	271330
15°	258479
20°	227895
25°	184330
30°	124687
35°	62476
40°	10141
45°	9920
50°	10114
55°	10267
60°	10555
65°	10807
70°	11053
75°	11187
80°	10759
85°	9026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 11187 cd/sqm



TEST NUMBER: P789257

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.6	11.6
10°-20°	632.1	31.3
20°-30°	680.1	33.7
30°-40°	295.6	14.7
40°-50°	49.6	2.5
50°-60°	48.3	2.4
60°-70°	41.3	2.0
70°-80°	27.6	1.4
80°-90°	8.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1545.7	76.7
0°-40°	1841.4	91.3
0°-60°	1939.3	96.2
0°-90°	2016.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2395	
5°	2444	234
15°	2285	632
25°	1529	680
35°	468	296
45°	64	50
55°	54	48
65°	42	41
75°	26	28
85°	7	8
90°	0	



TEST NUMBER: P789257

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2394.8
2.5°	2462.1
5°	2444.3
7.5°	2450.0
10°	2445.6
12.5°	2395.1
15°	2285.1
17.5°	2137.4
20°	1960.0
22.5°	1770.2
25°	1529.0
27.5°	1223.0
30°	988.3
32.5°	761.7
35°	468.4
37.5°	200.4
40°	71.1
42.5°	65.4
45°	64.2
47.5°	62.0
50°	59.5
52.5°	56.7
55°	53.9
57.5°	51.1
60°	48.3
62.5°	45.2
65°	41.8
67.5°	38.3
70°	34.6
72.5°	30.5
75°	26.5
77.5°	21.8
80°	17.1
82.5°	12.2
85°	7.2
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)