

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790515

Luminaire Tested: LER6D20D010-EC6DR6520359024-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D20D010-EC6DR6520359024-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2500.8 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P790515  
CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P790515

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132612
5°	132274
10°	132167
15°	128087
20°	116610
25°	101618
30°	84515
35°	66970
40°	48337
45°	30536
50°	15919
55°	8462
60°	4439
65°	2446
70°	1025
75°	1128
80°	774
85°	670

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30536 cd/sqm



TEST NUMBER: P790515

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.7	8.6
10°-20°	588.0	23.5
20°-30°	718.7	28.7
30°-40°	583.2	23.3
40°-50°	290.6	11.6
50°-60°	81.1	3.2
60°-70°	18.4	0.7
70°-80°	4.8	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1521.5	60.8
0°-40°	2104.6	84.2
0°-60°	2476.3	99.0
0°-90°	2500.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2500.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2271	
5°	2256	215
15°	2118	588
25°	1577	719
35°	939	583
45°	370	291
55°	83	81
65°	18	18
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P790515

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2270.6
2.5°	2268.9
5°	2256.2
7.5°	2248.9
10°	2228.6
12.5°	2187.2
15°	2118.4
17.5°	2011.0
20°	1876.2
22.5°	1730.7
25°	1576.9
27.5°	1412.4
30°	1253.2
32.5°	1096.1
35°	939.3
37.5°	782.8
40°	634.0
42.5°	494.5
45°	369.7
47.5°	257.6
50°	175.2
52.5°	120.8
55°	83.1
57.5°	56.1
60°	38.0
62.5°	26.4
65°	17.7
67.5°	9.0
70°	6.0
72.5°	5.7
75°	5.0
77.5°	3.3
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)