

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789264

Luminaire Tested: LER6D10D010-EC6DR600210IC9040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR600210IC9040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1973.5 lumens
Efficiency: N/A
Efficacy: 168.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789264

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789264

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256085
5°	262383
10°	265550
15°	252971
20°	223046
25°	180412
30°	122025
35°	61156
40°	9913
45°	9704
50°	9910
55°	10058
60°	10336
65°	10574
70°	10830
75°	10934
80°	10571
85°	8775

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 10934 cd/sqm



TEST NUMBER: P789264

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.6	11.6
10°-20°	618.6	31.3
20°-30°	665.6	33.7
30°-40°	289.3	14.7
40°-50°	48.6	2.5
50°-60°	47.3	2.4
60°-70°	40.4	2.0
70°-80°	27.1	1.4
80°-90°	8.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1512.8	76.7
0°-40°	1802.1	91.3
0°-60°	1898.0	96.2
0°-90°	1973.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1973.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2344	
5°	2392	229
15°	2236	619
25°	1496	666
35°	458	289
45°	63	49
55°	53	47
65°	41	40
75°	26	27
85°	7	8
90°	0	



TEST NUMBER: P789264

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2343.8
2.5°	2409.7
5°	2392.3
7.5°	2397.8
10°	2393.5
12.5°	2344.1
15°	2236.4
17.5°	2091.9
20°	1918.3
22.5°	1732.5
25°	1496.5
27.5°	1196.9
30°	967.2
32.5°	745.5
35°	458.5
37.5°	196.1
40°	69.5
42.5°	64.1
45°	62.8
47.5°	60.7
50°	58.3
52.5°	55.5
55°	52.8
57.5°	50.0
60°	47.3
62.5°	44.2
65°	40.9
67.5°	37.5
70°	33.9
72.5°	29.9
75°	25.9
77.5°	21.4
80°	16.8
82.5°	11.9
85°	7.0
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)