

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789270

Luminaire Tested: LER6D10D010-EC6DR600210IC9040-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789270  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR600210IC9040-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1974.3 lumens  
Efficiency: N/A  
Efficacy: 168.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P789270

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P789270

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57	57
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	215866
5°	215342
10°	222492
15°	222724
20°	204931
25°	174312
30°	132812
35°	93928
40°	55155
45°	22251
50°	7428
55°	3581
60°	1464
65°	207
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22251 cd/sqm



TEST NUMBER: P789270

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.4	9.6
10°-20°	545.5	27.6
20°-30°	652.9	33.1
30°-40°	436.7	22.1
40°-50°	129.5	6.6
50°-60°	18.6	0.9
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.8	70.3
0°-40°	1824.4	92.4
0°-60°	1972.5	99.9
0°-90°	1974.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1974.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1976	
5°	1963	189
15°	1969	545
25°	1446	653
35°	704	437
45°	144	129
55°	19	19
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P789270  
CATALOG NUMBER: LER6D10D010-EC6DR600210IC9040-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1975.7
2.5°	1973.2
5°	1963.4
7.5°	1990.0
10°	2005.4
12.5°	2002.6
15°	1969.0
17.5°	1889.7
20°	1762.5
22.5°	1609.8
25°	1445.9
27.5°	1261.2
30°	1052.7
32.5°	866.7
35°	704.2
37.5°	541.4
40°	386.7
42.5°	255.0
45°	144.0
47.5°	73.7
50°	43.7
52.5°	28.3
55°	18.8
57.5°	12.0
60°	6.7
62.5°	2.8
65°	0.8
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)