

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789272

Luminaire Tested: LER6D10D010-EC6DR600210IC9050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR600210IC9050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1950.2 lumens
Efficiency: N/A
Efficacy: 166.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789272

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P789272

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253070
5°	259290
10°	262421
15°	249996
20°	220418
25°	178278
30°	120587
35°	60422
40°	9799
45°	9596
50°	9791
55°	9925
60°	10205
65°	10445
70°	10702
75°	10807
80°	10445
85°	8650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 10807 cd/sqm



TEST NUMBER: P789272

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.9	11.6
10°-20°	611.3	31.3
20°-30°	657.7	33.7
30°-40°	285.9	14.7
40°-50°	48.0	2.5
50°-60°	46.7	2.4
60°-70°	39.9	2.0
70°-80°	26.7	1.4
80°-90°	8.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.0	76.7
0°-40°	1780.9	91.3
0°-60°	1875.6	96.2
0°-90°	1950.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1950.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2316	
5°	2364	226
15°	2210	611
25°	1479	658
35°	453	286
45°	62	48
55°	52	47
65°	40	40
75°	26	27
85°	7	8
90°	0	



TEST NUMBER: P789272

CATALOG NUMBER: LER6D10D010-EC6DR600210IC9050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2316.2
2.5°	2381.3
5°	2364.1
7.5°	2369.5
10°	2365.3
12.5°	2316.5
15°	2210.1
17.5°	2067.2
20°	1895.7
22.5°	1712.1
25°	1478.8
27.5°	1182.8
30°	955.8
32.5°	736.7
35°	453.0
37.5°	193.8
40°	68.7
42.5°	63.3
45°	62.1
47.5°	60.0
50°	57.6
52.5°	54.9
55°	52.1
57.5°	49.4
60°	46.7
62.5°	43.7
65°	40.4
67.5°	37.1
70°	33.5
72.5°	29.5
75°	25.6
77.5°	21.1
80°	16.6
82.5°	11.8
85°	6.9
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)