

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789285

Luminaire Tested: LER6D10D010-EC6DR650210IC9024-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P789285  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D10D010-EC6DR650210IC9024-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1532.7 lumens  
Efficiency: N/A  
Efficacy: 131.0 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P789285  
CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P789285

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81281
5°	81075
10°	81004
15°	78507
20°	71469
25°	62283
30°	51800
35°	41046
40°	29627
45°	18716
50°	9758
55°	5183
60°	2722
65°	1493
70°	632
75°	700
80°	471
85°	402

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18716 cd/sqm



TEST NUMBER: P789285

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.6	8.6
10°-20°	360.4	23.5
20°-30°	440.5	28.7
30°-40°	357.4	23.3
40°-50°	178.1	11.6
50°-60°	49.7	3.2
60°-70°	11.3	0.7
70°-80°	2.9	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	60.8
0°-40°	1290.0	84.2
0°-60°	1517.8	99.0
0°-90°	1532.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1532.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1392	
5°	1383	132
15°	1298	360
25°	966	441
35°	576	357
45°	227	178
55°	51	50
65°	11	11
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P789285

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9024-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1391.7
2.5°	1390.6
5°	1382.9
7.5°	1378.4
10°	1365.9
12.5°	1340.5
15°	1298.4
17.5°	1232.6
20°	1149.9
22.5°	1060.8
25°	966.5
27.5°	865.7
30°	768.1
32.5°	671.8
35°	575.7
37.5°	479.8
40°	388.6
42.5°	303.1
45°	226.6
47.5°	157.9
50°	107.4
52.5°	74.0
55°	50.9
57.5°	34.4
60°	23.3
62.5°	16.2
65°	10.8
67.5°	5.5
70°	3.7
72.5°	3.5
75°	3.1
77.5°	2.0
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)