

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790554

Luminaire Tested: LER6D20D010-EC6DR6520359050-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6520359050-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2712.8 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790554

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790554

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291835
5°	292073
10°	302362
15°	302854
20°	278834
25°	237580
30°	181877
35°	128488
40°	75851
45°	30795
50°	11168
55°	6210
60°	3562
65°	1965
70°	2076
75°	1604
80°	1699
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30795 cd/sqm



TEST NUMBER: P790554

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.2	9.5
10°-20°	741.9	27.3
20°-30°	890.1	32.8
30°-40°	598.2	22.1
40°-50°	179.1	6.6
50°-60°	31.6	1.2
60°-70°	9.0	0.3
70°-80°	4.4	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1889.2	69.6
0°-40°	2487.4	91.7
0°-60°	2698.0	99.5
0°-90°	2712.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2712.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2671	
5°	2663	257
15°	2677	742
25°	1971	890
35°	963	598
45°	199	179
55°	33	32
65°	8	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P790554

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2671.0
2.5°	2682.4
5°	2663.0
7.5°	2703.2
10°	2725.3
12.5°	2719.9
15°	2677.4
17.5°	2573.4
20°	2398.1
22.5°	2191.6
25°	1970.7
27.5°	1721.3
30°	1441.6
32.5°	1188.0
35°	963.3
37.5°	741.3
40°	531.8
42.5°	347.3
45°	199.3
47.5°	105.5
50°	65.7
52.5°	45.5
55°	32.6
57.5°	23.5
60°	16.3
62.5°	10.6
65°	7.6
67.5°	6.8
70°	6.5
72.5°	4.9
75°	3.8
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)