

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790555

Luminaire Tested: LER6D20D010-EC6DR6520359050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6520359050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3073.0 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790555

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P790555

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162958
5°	162543
10°	162406
15°	157400
20°	143292
25°	124868
30°	103856
35°	82292
40°	59392
45°	37523
50°	19562
55°	10396
60°	5455
65°	2999
70°	1264
75°	1399
80°	975
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37523 cd/sqm



TEST NUMBER: P790555

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.9	8.6
10°-20°	722.6	23.5
20°-30°	883.2	28.7
30°-40°	716.6	23.3
40°-50°	357.1	11.6
50°-60°	99.6	3.2
60°-70°	22.6	0.7
70°-80°	5.9	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1869.6	60.8
0°-40°	2586.2	84.2
0°-60°	3042.9	99.0
0°-90°	3073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3073.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2790	
5°	2772	264
15°	2603	723
25°	1938	883
35°	1154	717
45°	454	357
55°	102	100
65°	22	23
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P790555

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2790.2
2.5°	2788.1
5°	2772.5
7.5°	2763.5
10°	2738.5
12.5°	2687.7
15°	2603.2
17.5°	2471.2
20°	2305.5
22.5°	2126.8
25°	1937.7
27.5°	1735.6
30°	1540.0
32.5°	1346.9
35°	1154.2
37.5°	961.9
40°	779.0
42.5°	607.6
45°	454.3
47.5°	316.5
50°	215.3
52.5°	148.4
55°	102.1
57.5°	68.9
60°	46.7
62.5°	32.4
65°	21.7
67.5°	11.1
70°	7.4
72.5°	7.0
75°	6.2
77.5°	4.1
80°	2.9
82.5°	2.1
85°	1.2
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)