

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790557

Luminaire Tested: LER6D20D010-EC6DR6520359050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6520359050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3475.2 lumens
Efficiency: N/A
Efficacy: 150.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790557

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790557

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184288
5°	183825
10°	183667
15°	178006
20°	162049
25°	141217
30°	117452
35°	93065
40°	67168
45°	42438
50°	22115
55°	11761
60°	6179
65°	3400
70°	1417
75°	1580
80°	1076
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42438 cd/sqm



TEST NUMBER: P790557

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.4	8.6
10°-20°	817.1	23.5
20°-30°	998.8	28.7
30°-40°	810.4	23.3
40°-50°	403.9	11.6
50°-60°	112.7	3.2
60°-70°	25.6	0.7
70°-80°	6.7	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2114.4	60.8
0°-40°	2924.8	84.2
0°-60°	3441.3	99.0
0°-90°	3475.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3475.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3155	
5°	3136	298
15°	2944	817
25°	2191	999
35°	1305	810
45°	514	404
55°	116	113
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P790557

CATALOG NUMBER: LER6D20D010-EC6DR6520359050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3155.4
2.5°	3153.1
5°	3135.5
7.5°	3125.3
10°	3097.0
12.5°	3039.5
15°	2944.0
17.5°	2794.7
20°	2607.3
22.5°	2405.2
25°	2191.4
27.5°	1962.8
30°	1741.6
32.5°	1523.2
35°	1305.3
37.5°	1087.8
40°	881.0
42.5°	687.2
45°	513.8
47.5°	358.0
50°	243.4
52.5°	167.9
55°	115.5
57.5°	77.9
60°	52.9
62.5°	36.6
65°	24.6
67.5°	12.5
70°	8.3
72.5°	7.9
75°	7.0
77.5°	4.6
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)