

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P789289

Luminaire Tested: LER6D10D010-EC6DR650210IC9027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P789289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D10D010-EC6DR650210IC9027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1616.3 lumens
Efficiency: N/A
Efficacy: 138.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P789289

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P789289

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173878
5°	174026
10°	180155
15°	180452
20°	166131
25°	141557
30°	108362
35°	76562
40°	45185
45°	18341
50°	6646
55°	3696
60°	2120
65°	1163
70°	1214
75°	971
80°	1007
85°	878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18341 cd/sqm



TEST NUMBER: P789289

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	9.5
10°-20°	442.0	27.3
20°-30°	530.4	32.8
30°-40°	356.4	22.1
40°-50°	106.7	6.6
50°-60°	18.8	1.2
60°-70°	5.3	0.3
70°-80°	2.6	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.6	69.6
0°-40°	1482.1	91.7
0°-60°	1607.5	99.5
0°-90°	1616.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1616.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1591	
5°	1587	153
15°	1595	442
25°	1174	530
35°	574	356
45°	119	107
55°	19	19
65°	4	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P789289

CATALOG NUMBER: LER6D10D010-EC6DR650210IC9027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1591.4
2.5°	1598.2
5°	1586.7
7.5°	1610.7
10°	1623.8
12.5°	1620.6
15°	1595.3
17.5°	1533.3
20°	1428.8
22.5°	1305.8
25°	1174.2
27.5°	1025.6
30°	858.9
32.5°	707.9
35°	574.0
37.5°	441.7
40°	316.8
42.5°	206.9
45°	118.7
47.5°	62.9
50°	39.1
52.5°	27.1
55°	19.4
57.5°	14.0
60°	9.7
62.5°	6.3
65°	4.5
67.5°	4.1
70°	3.8
72.5°	2.9
75°	2.3
77.5°	2.0
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)