

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790570

Luminaire Tested: LER6D20D010-EC6DR7020359027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P790570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR7020359027-6LBDDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2555.8 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790570
CATALOG NUMBER: LER6D20D010-EC6DR7020359027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790570

CATALOG NUMBER: LER6D20D010-EC6DR7020359027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313950
5°	304620
10°	296138
15°	292244
20°	272904
25°	205017
30°	144924
35°	51339
40°	27000
45°	28756
50°	29780
55°	30326
60°	30527
65°	29886
70°	28208
75°	26131
80°	23218
85°	18804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 30527 cd/sqm



TEST NUMBER: P790570

CATALOG NUMBER: LER6D20D010-EC6DR7020359027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.0	10.3
10°-20°	718.6	28.1
20°-30°	791.4	31.0
30°-40°	302.4	11.8
40°-50°	142.8	5.6
50°-60°	141.9	5.6
60°-70°	113.7	4.4
70°-80°	65.3	2.6
80°-90°	17.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.0	69.3
0°-40°	2074.3	81.2
0°-60°	2359.1	92.3
0°-90°	2555.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2873	
5°	2777	262
15°	2584	719
25°	1701	791
35°	385	302
45°	186	143
55°	159	142
65°	116	114
75°	62	65
85°	15	18
90°	0	



TEST NUMBER: P790570

CATALOG NUMBER: LER6D20D010-EC6DR7020359027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2873.4
2.5°	2843.4
5°	2777.4
7.5°	2722.4
10°	2669.2
12.5°	2624.1
15°	2583.6
17.5°	2485.8
20°	2347.1
22.5°	2047.7
25°	1700.6
27.5°	1480.4
30°	1148.7
32.5°	742.0
35°	384.9
37.5°	207.9
40°	189.3
42.5°	187.9
45°	186.1
47.5°	182.0
50°	175.2
52.5°	167.4
55°	159.2
57.5°	150.1
60°	139.7
62.5°	127.8
65°	115.6
67.5°	101.9
70°	88.3
72.5°	74.6
75°	61.9
77.5°	48.7
80°	36.9
82.5°	25.9
85°	15.0
87.5°	5.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)